

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856574

Luminaire Tested: **LD6C100D010 EU61009030 6LBWLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P856574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C100D010 EU61009030 6LBWLI
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10467.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856574

CATALOG NUMBER: LD6C100D010 EU61009030 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856574

CATALOG NUMBER: LD6C100D010 EU61009030 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	358469
5°	361786
10°	371909
15°	381217
20°	386999
25°	379008
30°	355333
35°	317691
40°	257318
45°	170219
50°	86036
55°	36300
60°	11699
65°	4592
70°	3831
75°	2521
80°	0
85°	0



TEST NUMBER: P856574

CATALOG NUMBER: LD6C100D010 EU61009030 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.8	6.0
10°-20°	1896.0	18.1
20°-30°	2858.2	27.3
30°-40°	2925.5	27.9
40°-50°	1704.3	16.3
50°-60°	391.7	3.7
60°-70°	48.0	0.5
70°-80°	12.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5385.0	51.4
0°-40°	8310.5	79.4
0°-60°	10406.4	99.4
0°-90°	10467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10467.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6539	
5°	6574	631
15°	6717	1896
25°	6266	2858
35°	4747	2925
45°	2196	1704
55°	380	392
65°	35	48
75°	12	13
85°	0	0
90°	0	



TEST NUMBER: P856574

CATALOG NUMBER: LD6C100D010 EU61009030 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6539.0
2.5°	6527.1
5°	6574.4
7.5°	6621.8
10°	6681.1
12.5°	6693.1
15°	6717.0
17.5°	6693.1
20°	6633.7
22.5°	6443.8
25°	6265.9
27.5°	5981.3
30°	5613.4
32.5°	5233.6
35°	4747.1
37.5°	4200.9
40°	3595.7
42.5°	2919.4
45°	2195.6
47.5°	1530.7
50°	1008.8
52.5°	641.0
55°	379.8
57.5°	201.9
60°	106.7
62.5°	59.3
65°	35.4
67.5°	35.4
70°	23.9
72.5°	11.9
75°	11.9
77.5°	11.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)