

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683877

Luminaire Tested: **LX6C100D010 EX6C1009030 6LBMH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P683877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX6C1009030 6LBMH
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7572.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683877

CATALOG NUMBER: LX6C100D010 EX6C1009030 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P683877

CATALOG NUMBER: LX6C100D010 EX6C1009030 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	410806
5°	403449
10°	382836
15°	358998
20°	334337
25°	308056
30°	256685
35°	180913
40°	115302
45°	68759
50°	40587
55°	25825
60°	17784
65°	12621
70°	8687
75°	6863
80°	3378
85°	0



TEST NUMBER: P683877

CATALOG NUMBER: LX6C100D010 EX6C1009030 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	685.2	9.0
10°-20°	1772.5	23.4
20°-30°	2296.7	30.3
30°-40°	1705.1	22.5
40°-50°	719.8	9.5
50°-60°	255.6	3.4
60°-70°	98.7	1.3
70°-80°	34.1	0.5
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4754.4	62.8
0°-40°	6459.5	85.3
0°-60°	7434.9	98.2
0°-90°	7572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7572.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7494	
5°	7332	685
15°	6326	1773
25°	5093	2297
35°	2703	1705
45°	887	720
55°	270	256
65°	97	99
75°	32	34
85°	0	4
90°	0	



TEST NUMBER: P683877

CATALOG NUMBER: LX6C100D010 EX6C1009030 6LBMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7493.7
2.5°	7471.9
5°	7331.5
7.5°	7125.8
10°	6877.4
12.5°	6606.8
15°	6325.5
17.5°	6012.3
20°	5731.0
22.5°	5439.1
25°	5092.9
27.5°	4617.1
30°	4055.0
32.5°	3395.2
35°	2703.3
37.5°	2119.5
40°	1611.2
42.5°	1200.1
45°	886.9
47.5°	648.7
50°	475.9
52.5°	356.8
55°	270.2
57.5°	205.3
60°	162.2
62.5°	119.1
65°	97.3
67.5°	75.5
70°	54.2
72.5°	43.1
75°	32.4
77.5°	21.8
80°	10.7
82.5°	10.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)