

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684996

Luminaire Tested: **LX6C40D010 EX6409030 6LRMDLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C40D010 EX6409030 6LRMDLI
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3087.1 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684996

CATALOG NUMBER: LX6C40D010 EX6409030 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P684996

CATALOG NUMBER: LX6C40D010 EX6409030 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252765
5°	253252
10°	241350
15°	207816
20°	171200
25°	133719
30°	96572
35°	49456
40°	24117
45°	10017
50°	1825
55°	1061
60°	691
65°	519
70°	385
75°	339
80°	253
85°	0



TEST NUMBER: P684996

CATALOG NUMBER: LX6C40D010 EX6409030 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	431.4	14.0
10°-20°	1014.9	32.9
20°-30°	1005.2	32.6
30°-40°	509.6	16.5
40°-50°	109.8	3.6
50°-60°	10.5	0.3
60°-70°	4.0	0.1
70°-80°	1.5	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2451.4	79.4
0°-40°	2961.0	95.9
0°-60°	3081.2	99.8
0°-90°	3087.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3087.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4611	
5°	4602	431
15°	3662	1015
25°	2211	1005
35°	739	510
45°	129	110
55°	11	10
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P684996

CATALOG NUMBER: LX6C40D010 EX6409030 6LRMDLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4610.8
2.5°	4616.4
5°	4602.1
7.5°	4529.9
10°	4335.7
12.5°	4023.3
15°	3661.7
17.5°	3291.4
20°	2934.6
22.5°	2577.8
25°	2210.7
27.5°	1836.4
30°	1525.6
32.5°	1175.1
35°	739.0
37.5°	497.2
40°	337.0
42.5°	218.1
45°	129.2
47.5°	57.9
50°	21.4
52.5°	14.3
55°	11.1
57.5°	7.9
60°	6.3
62.5°	4.8
65°	4.0
67.5°	3.2
70°	2.4
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)