

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684776

Luminaire Tested: **LX6C100D010 EX61009035 6LBMLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684776  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C100D010 EX61009035 6LBMLI  
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9397.0 lumens  
Efficiency: N/A  
Efficacy: 82.1 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684776

CATALOG NUMBER: LX6C100D010 EX61009035 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684776

CATALOG NUMBER: LX6C100D010 EX61009035 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	644680
5°	638547
10°	605082
15°	549356
20°	485440
25°	419673
30°	328057
35°	201184
40°	103258
45°	41028
50°	13322
55°	4588
60°	3936
65°	3139
70°	1939
75°	2563
80°	0
85°	0



TEST NUMBER: P684776

CATALOG NUMBER: LX6C100D010 EX61009035 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1083.3	11.5
10°-20°	2697.1	28.7
20°-30°	3135.3	33.4
30°-40°	1920.0	20.4
40°-50°	476.8	5.1
50°-60°	55.7	0.6
60°-70°	20.8	0.2
70°-80°	7.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6915.8	73.6
0°-40°	8835.8	94.0
0°-60°	9368.2	99.7
0°-90°	9397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9397.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11760	
5°	11604	###
15°	9680	2697
25°	6938	3135
35°	3006	1920
45°	529	477
55°	48	56
65°	24	21
75°	12	8
85°	0	0
90°	0	



TEST NUMBER: P684776

CATALOG NUMBER: LX6C100D010 EX61009035 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	11759.9
2.5°	11747.8
5°	11603.7
7.5°	11290.9
10°	10869.9
12.5°	10316.9
15°	9679.6
17.5°	8994.3
20°	8321.1
22.5°	7647.4
25°	6938.2
27.5°	6120.5
30°	5182.5
32.5°	4088.3
35°	3006.2
37.5°	2116.2
40°	1442.9
42.5°	901.7
45°	529.2
47.5°	300.7
50°	156.2
52.5°	72.3
55°	48.0
57.5°	35.9
60°	35.9
62.5°	24.2
65°	24.2
67.5°	12.1
70°	12.1
72.5°	12.1
75°	12.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)