

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683906

Luminaire Tested: **LX6C100D010 EX6C1009040 6LBMDH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P683906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C100D010 EX6C1009040 6LBMDH
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7607.9 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 114.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P683906

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P683906

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	548180
5°	531217
10°	489158
15°	438743
20°	390377
25°	324182
30°	231605
35°	148877
40°	90720
45°	50432
50°	22345
55°	12941
60°	8519
65°	6045
70°	4264
75°	3283
80°	2115
85°	1384



TEST NUMBER: P683906

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	893.5	11.7
10°-20°	2162.8	28.4
20°-30°	2405.3	31.6
30°-40°	1425.2	18.7
40°-50°	522.1	6.9
50°-60°	131.2	1.7
60°-70°	47.9	0.6
70°-80°	16.7	0.2
80°-90°	3.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5461.6	71.8
0°-40°	6886.8	90.5
0°-60°	7540.1	99.1
0°-90°	7607.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7607.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10000	
5°	9653	894
15°	7731	2163
25°	5360	2405
35°	2225	1425
45°	650	522
55°	135	131
65°	47	48
75°	16	17
85°	2	3
90°	0	



TEST NUMBER: P683906

CATALOG NUMBER: LX6C100D010 EX6C1009040 6LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9999.6
2.5°	9910.8
5°	9653.3
7.5°	9262.5
10°	8787.4
12.5°	8263.5
15°	7730.6
17.5°	7213.3
20°	6691.6
22.5°	6085.5
25°	5359.5
27.5°	4524.7
30°	3658.8
32.5°	2884.0
35°	2224.6
37.5°	1689.5
40°	1267.7
42.5°	923.6
45°	650.5
47.5°	413.0
50°	262.0
52.5°	184.3
55°	135.4
57.5°	102.1
60°	77.7
62.5°	59.9
65°	46.6
67.5°	35.5
70°	26.6
72.5°	20.0
75°	15.5
77.5°	11.1
80°	6.7
82.5°	4.4
85°	2.2
87.5°	2.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)