

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683926

Luminaire Tested: **LX6C100D010 EX6C1009050 6LBWH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P683926  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C100D010 EX6C1009050 6LBWH  
Description: 6 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9497.0 lumens  
Efficiency: N/A  
Efficacy: 83.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683926

CATALOG NUMBER: LX6C100D010 EX6C1009050 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P683926

CATALOG NUMBER: LX6C100D010 EX6C1009050 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	321104
5°	320993
10°	318520
15°	316387
20°	311568
25°	304451
30°	286658
35°	259427
40°	216627
45°	165994
50°	117557
55°	74119
60°	41806
65°	27136
70°	17727
75°	13026
80°	7829
85°	7799



TEST NUMBER: P683926

CATALOG NUMBER: LX6C100D010 EX6C1009050 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	553.2	5.8
10°-20°	1569.8	16.5
20°-30°	2301.7	24.2
30°-40°	2395.5	25.2
40°-50°	1657.3	17.5
50°-60°	721.6	7.6
60°-70°	221.3	2.3
70°-80°	66.3	0.7
80°-90°	10.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4424.8	46.6
0°-40°	6820.3	71.8
0°-60°	9199.3	96.9
0°-90°	9497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9497.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5857	
5°	5833	553
15°	5575	1570
25°	5033	2302
35°	3876	2396
45°	2141	1657
55°	776	722
65°	209	221
75°	62	66
85°	12	10
90°	0	



TEST NUMBER: P683926

CATALOG NUMBER: LX6C100D010 EX6C1009050 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5857.4
2.5°	5869.8
5°	5833.1
7.5°	5784.0
10°	5722.0
12.5°	5660.5
15°	5574.7
17.5°	5463.7
20°	5340.7
22.5°	5205.4
25°	5033.3
27.5°	4811.6
30°	4528.5
32.5°	4233.0
35°	3876.5
37.5°	3482.8
40°	3027.1
42.5°	2571.9
45°	2141.1
47.5°	1735.0
50°	1378.4
52.5°	1046.2
55°	775.5
57.5°	553.8
60°	381.3
62.5°	283.1
65°	209.2
67.5°	160.1
70°	110.6
72.5°	86.3
75°	61.5
77.5°	36.7
80°	24.8
82.5°	12.4
85°	12.4
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)