

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684791

Luminaire Tested: **LX6C120D010 EX61209027 6LBMLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684791  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C120D010 EX61209027 6LBMLI  
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10662.9 lumens  
Efficiency: N/A  
Efficacy: 74.9 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 142.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684791

CATALOG NUMBER: LX6C120D010 EX61209027 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684791

CATALOG NUMBER: LX6C120D010 EX61209027 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82	82	82	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71	71	71	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63	63	63	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	731531
5°	724574
10°	686599
15°	623369
20°	550837
25°	476217
30°	372253
35°	228288
40°	117170
45°	46547
50°	15113
55°	5209
60°	4462
65°	3567
70°	2196
75°	2902
80°	0
85°	0



TEST NUMBER: P684791

CATALOG NUMBER: LX6C120D010 EX61209027 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1229.3	11.5
10°-20°	3060.5	28.7
20°-30°	3557.7	33.4
30°-40°	2178.6	20.4
40°-50°	541.0	5.1
50°-60°	63.2	0.6
60°-70°	23.6	0.2
70°-80°	9.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7847.5	73.6
0°-40°	10026.2	94.0
0°-60°	10630.3	99.7
0°-90°	10662.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10662.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13344	
5°	13167	###
15°	10984	3061
25°	7873	3558
35°	3411	2179
45°	600	541
55°	54	63
65°	28	24
75°	14	9
85°	0	0
90°	0	



TEST NUMBER: P684791

CATALOG NUMBER: LX6C120D010 EX61209027 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13344.2
2.5°	13330.5
5°	13167.0
7.5°	12812.0
10°	12334.3
12.5°	11706.9
15°	10983.7
17.5°	10206.0
20°	9442.1
22.5°	8677.7
25°	7873.0
27.5°	6945.1
30°	5880.7
32.5°	4639.1
35°	3411.2
37.5°	2401.3
40°	1637.3
42.5°	1023.2
45°	600.4
47.5°	341.2
50°	177.2
52.5°	82.0
55°	54.5
57.5°	40.7
60°	40.7
62.5°	27.5
65°	27.5
67.5°	13.7
70°	13.7
72.5°	13.7
75°	13.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)