

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683968

Luminaire Tested: **LX6C120D010 EX6C1209040 6LBMDH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P683968  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C120D010 EX6C1209040 6LBMDH  
Description: 6 INCH 12000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9101.1 lumens  
Efficiency: N/A  
Efficacy: 64.0 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 142.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683968

CATALOG NUMBER: LX6C120D010 EX6C1209040 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P683968

CATALOG NUMBER: LX6C120D010 EX6C1209040 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	655759
5°	635460
10°	585154
15°	524844
20°	466981
25°	387797
30°	277055
35°	178096
40°	108525
45°	60332
50°	26728
55°	15483
60°	10197
65°	7238
70°	5113
75°	3940
80°	2526
85°	1698



TEST NUMBER: P683968

CATALOG NUMBER: LX6C120D010 EX6C1209040 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1068.9	11.7
10°-20°	2587.3	28.4
20°-30°	2877.3	31.6
30°-40°	1704.9	18.7
40°-50°	624.5	6.9
50°-60°	156.9	1.7
60°-70°	57.3	0.6
70°-80°	19.9	0.2
80°-90°	4.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6533.4	71.8
0°-40°	8238.3	90.5
0°-60°	9019.8	99.1
0°-90°	9101.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9101.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11962	
5°	11548	###
15°	9248	2587
25°	6411	2877
35°	2661	1705
45°	778	625
55°	162	157
65°	56	57
75°	19	20
85°	3	4
90°	0	



TEST NUMBER: P683968

CATALOG NUMBER: LX6C120D010 EX6C1209040 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11962.0
2.5°	11855.7
5°	11547.6
7.5°	11080.2
10°	10511.9
12.5°	9885.1
15°	9247.7
17.5°	8628.9
20°	8004.7
22.5°	7279.7
25°	6411.2
27.5°	5412.6
30°	4376.8
32.5°	3450.0
35°	2661.2
37.5°	2021.1
40°	1516.5
42.5°	1104.8
45°	778.2
47.5°	494.0
50°	313.4
52.5°	220.4
55°	162.0
57.5°	122.2
60°	93.0
62.5°	71.7
65°	55.8
67.5°	42.5
70°	31.9
72.5°	23.9
75°	18.6
77.5°	13.3
80°	8.0
82.5°	5.3
85°	2.7
87.5°	2.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)