

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685012

Luminaire Tested: **LX6C45D010 EX6459027 6LBMLI**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P685012  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C45D010 EX6459027 6LBMLI  
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4098.1 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685012

CATALOG NUMBER: LX6C45D010 EX6459027 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685012

CATALOG NUMBER: LX6C45D010 EX6459027 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	281140
5°	278466
10°	263873
15°	239576
20°	211698
25°	183017
30°	143066
35°	87736
40°	45034
45°	17893
50°	5808
55°	1998
60°	1721
65°	1375
70°	850
75°	1123
80°	0
85°	0



TEST NUMBER: P685012

CATALOG NUMBER: LX6C45D010 EX6459027 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	472.4	11.5
10°-20°	1176.2	28.7
20°-30°	1367.3	33.4
30°-40°	837.3	20.4
40°-50°	207.9	5.1
50°-60°	24.3	0.6
60°-70°	9.1	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3015.9	73.6
0°-40°	3853.3	94.0
0°-60°	4085.5	99.7
0°-90°	4098.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4098.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5128	
5°	5060	472
15°	4221	1176
25°	3026	1367
35°	1311	837
45°	231	208
55°	21	24
65°	11	9
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P685012

CATALOG NUMBER: LX6C45D010 EX6459027 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5128.4
2.5°	5123.2
5°	5060.3
7.5°	4923.9
10°	4740.3
12.5°	4499.2
15°	4221.3
17.5°	3922.4
20°	3628.8
22.5°	3335.0
25°	3025.7
27.5°	2669.1
30°	2260.1
32.5°	1782.9
35°	1311.0
37.5°	922.9
40°	629.3
42.5°	393.2
45°	230.8
47.5°	131.1
50°	68.1
52.5°	31.5
55°	20.9
57.5°	15.7
60°	15.7
62.5°	10.6
65°	10.6
67.5°	5.3
70°	5.3
72.5°	5.3
75°	5.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)