

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684295

Luminaire Tested: **LX6C45D010 EX6C459030 6LBMDH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C45D010 EX6C459030 6LBMDH
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3443.9 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684295

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P684295

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248149
5°	240474
10°	221433
15°	198611
20°	176719
25°	146748
30°	104845
35°	67392
40°	41070
45°	22832
50°	10115
55°	5859
60°	3859
65°	2737
70°	1939
75°	1483
80°	947
85°	629



TEST NUMBER: P684295

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	404.5	11.7
10°-20°	979.1	28.4
20°-30°	1088.8	31.6
30°-40°	645.2	18.7
40°-50°	236.3	6.9
50°-60°	59.4	1.7
60°-70°	21.7	0.6
70°-80°	7.5	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2472.4	71.8
0°-40°	3117.5	90.5
0°-60°	3413.3	99.1
0°-90°	3443.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3443.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4527	
5°	4370	404
15°	3500	979
25°	2426	1089
35°	1007	645
45°	294	236
55°	61	59
65°	21	22
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P684295

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4526.6
2.5°	4486.4
5°	4369.9
7.5°	4193.0
10°	3977.9
12.5°	3740.7
15°	3499.5
17.5°	3265.3
20°	3029.2
22.5°	2754.8
25°	2426.1
27.5°	2048.2
30°	1656.3
32.5°	1305.5
35°	1007.0
37.5°	764.8
40°	573.9
42.5°	418.1
45°	294.5
47.5°	186.9
50°	118.6
52.5°	83.4
55°	61.3
57.5°	46.2
60°	35.2
62.5°	27.1
65°	21.1
67.5°	16.1
70°	12.1
72.5°	9.0
75°	7.0
77.5°	5.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)