

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684305

Luminaire Tested: **LX6C45D010 EX6C459035 6LBSH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684305  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C45D010 EX6C459035 6LBSH  
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5030.0 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684305

CATALOG NUMBER: LX6C45D010 EX6C459035 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684305

CATALOG NUMBER: LX6C45D010 EX6C459035 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144215
5°	143545
10°	140579
15°	135466
20°	129237
25°	122275
30°	115334
35°	108596
40°	102256
45°	95320
50°	86914
55°	76757
60°	64973
65°	51017
70°	36400
75°	19931
80°	3504
85°	0



TEST NUMBER: P684305

CATALOG NUMBER: LX6C45D010 EX6C459035 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	246.4	4.9
10°-20°	669.7	13.3
20°-30°	930.1	18.5
30°-40°	1015.0	20.2
40°-50°	946.8	18.8
50°-60°	718.7	14.3
60°-70°	393.5	7.8
70°-80°	108.3	2.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1846.2	36.7
0°-40°	2861.2	56.9
0°-60°	4526.7	90.0
0°-90°	5030.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5030.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2631	
5°	2608	246
15°	2387	670
25°	2022	930
35°	1623	1015
45°	1230	947
55°	803	719
65°	393	394
75°	94	108
85°	0	2
90°	0	



TEST NUMBER: P684305

CATALOG NUMBER: LX6C45D010 EX6C459035 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2630.7
2.5°	2630.7
5°	2608.5
7.5°	2575.2
10°	2525.4
12.5°	2459.0
15°	2386.9
17.5°	2298.3
20°	2215.3
22.5°	2115.6
25°	2021.5
27.5°	1927.3
30°	1822.0
32.5°	1722.3
35°	1622.7
37.5°	1523.0
40°	1428.9
42.5°	1329.2
45°	1229.5
47.5°	1129.8
50°	1019.1
52.5°	913.8
55°	803.1
57.5°	697.8
60°	592.6
62.5°	487.4
65°	393.3
67.5°	304.6
70°	227.1
72.5°	155.1
75°	94.1
77.5°	44.4
80°	11.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)