

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684319

Luminaire Tested: **LX6C45D010 EX6C459050 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684319
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C45D010 EX6C459050 6LBSH
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5141.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684319

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684319

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147395
5°	146709
10°	143685
15°	138457
20°	132090
25°	124973
30°	117879
35°	110999
40°	104510
45°	97421
50°	88833
55°	78449
60°	66398
65°	52133
70°	37202
75°	20376
80°	3599
85°	0



TEST NUMBER: P684319

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.8	4.9
10°-20°	684.5	13.3
20°-30°	950.6	18.5
30°-40°	1037.4	20.2
40°-50°	967.7	18.8
50°-60°	734.5	14.3
60°-70°	402.2	7.8
70°-80°	110.7	2.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1887.0	36.7
0°-40°	2924.4	56.9
0°-60°	4626.6	90.0
0°-90°	5141.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5141.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2689	
5°	2666	252
15°	2440	685
25°	2066	951
35°	1659	1037
45°	1257	968
55°	821	735
65°	402	402
75°	96	111
85°	0	2
90°	0	



TEST NUMBER: P684319

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2688.7
2.5°	2688.7
5°	2666.0
7.5°	2632.1
10°	2581.2
12.5°	2513.2
15°	2439.6
17.5°	2349.1
20°	2264.2
22.5°	2162.3
25°	2066.1
27.5°	1969.8
30°	1862.2
32.5°	1760.3
35°	1658.6
37.5°	1556.7
40°	1460.4
42.5°	1358.5
45°	1256.6
47.5°	1154.7
50°	1041.6
52.5°	934.0
55°	820.8
57.5°	713.2
60°	605.6
62.5°	498.2
65°	401.9
67.5°	311.3
70°	232.1
72.5°	158.5
75°	96.2
77.5°	45.3
80°	11.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)