

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684320

Luminaire Tested: **LX6C45D010 EX6C459050 6LBWH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684320  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C45D010 EX6C459050 6LBWH  
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4366.0 lumens  
Efficiency: N/A  
Efficacy: 88.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 49.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684320

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P684320

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147620
5°	147567
10°	146435
15°	145449
20°	143238
25°	139962
30°	131786
35°	119264
40°	99587
45°	76310
50°	54045
55°	34073
60°	19220
65°	12479
70°	8142
75°	5994
80°	3599
85°	3585



TEST NUMBER: P684320

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	254.3	5.8
10°-20°	721.7	16.5
20°-30°	1058.2	24.2
30°-40°	1101.3	25.2
40°-50°	761.9	17.5
50°-60°	331.8	7.6
60°-70°	101.7	2.3
70°-80°	30.5	0.7
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2034.2	46.6
0°-40°	3135.4	71.8
0°-60°	4229.1	96.9
0°-90°	4366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4366.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2693	
5°	2682	254
15°	2563	722
25°	2314	1058
35°	1782	1101
45°	984	762
55°	356	332
65°	96	102
75°	28	31
85°	6	5
90°	0	



TEST NUMBER: P684320

CATALOG NUMBER: LX6C45D010 EX6C459050 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2692.8
2.5°	2698.5
5°	2681.6
7.5°	2659.0
10°	2630.6
12.5°	2602.3
15°	2562.8
17.5°	2511.8
20°	2455.3
22.5°	2393.0
25°	2313.9
27.5°	2212.0
30°	2081.9
32.5°	1946.0
35°	1782.1
37.5°	1601.1
40°	1391.6
42.5°	1182.4
45°	984.3
47.5°	797.6
50°	633.7
52.5°	481.0
55°	356.5
57.5°	254.6
60°	175.3
62.5°	130.2
65°	96.2
67.5°	73.6
70°	50.8
72.5°	39.7
75°	28.3
77.5°	16.9
80°	11.4
82.5°	5.7
85°	5.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)