

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563952

Luminaire Tested: **LX6C45D010 EX6C459030 6LBWH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C45D010 EX6C459030 6LBWH
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4213.0 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563952

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P563952

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142445
5°	142395
10°	141302
15°	140353
20°	138215
25°	135056
30°	127165
35°	115088
40°	96101
45°	73636
50°	52152
55°	32878
60°	18551
65°	12038
70°	7870
75°	5782
80°	3473
85°	3459



TEST NUMBER: P563952

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.4	5.8
10°-20°	696.4	16.5
20°-30°	1021.1	24.2
30°-40°	1062.7	25.2
40°-50°	735.2	17.5
50°-60°	320.1	7.6
60°-70°	98.2	2.3
70°-80°	29.5	0.7
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1962.9	46.6
0°-40°	3025.6	71.8
0°-60°	4080.9	96.9
0°-90°	4213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4213.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2598	
5°	2588	245
15°	2473	696
25°	2233	1021
35°	1720	1063
45°	950	735
55°	344	320
65°	93	98
75°	27	29
85°	6	4
90°	0	



TEST NUMBER: P563952

CATALOG NUMBER: LX6C45D010 EX6C459030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2598.4
2.5°	2603.9
5°	2587.6
7.5°	2565.8
10°	2538.4
12.5°	2511.1
15°	2473.0
17.5°	2423.8
20°	2369.2
22.5°	2309.2
25°	2232.8
27.5°	2134.5
30°	2008.9
32.5°	1877.8
35°	1719.7
37.5°	1545.0
40°	1342.9
42.5°	1140.9
45°	949.8
47.5°	769.7
50°	611.5
52.5°	464.1
55°	344.0
57.5°	245.7
60°	169.2
62.5°	125.6
65°	92.8
67.5°	71.0
70°	49.1
72.5°	38.3
75°	27.3
77.5°	16.3
80°	11.0
82.5°	5.5
85°	5.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)