

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685042

Luminaire Tested: **LX6C05D010 EX6059030 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C05D010 EX6059030 6LBMLI
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685042

CATALOG NUMBER: LX6C05D010 EX6059030 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685042

CATALOG NUMBER: LX6C05D010 EX6059030 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41027
5°	40634
10°	38504
15°	34960
20°	30890
25°	26705
30°	20877
35°	12802
40°	6569
45°	2613
50°	844
55°	296
60°	252
65°	195
70°	128
75°	169
80°	0
85°	0



TEST NUMBER: P685042

CATALOG NUMBER: LX6C05D010 EX6059030 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	11.5
10°-20°	171.6	28.7
20°-30°	199.5	33.4
30°-40°	122.2	20.4
40°-50°	30.3	5.1
50°-60°	3.6	0.6
60°-70°	1.3	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	440.1	73.6
0°-40°	562.3	94.0
0°-60°	596.2	99.7
0°-90°	598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	748	
5°	738	69
15°	616	172
25°	442	200
35°	191	122
45°	34	30
55°	3	4
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P685042

CATALOG NUMBER: LX6C05D010 EX6059030 6LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	748.4
2.5°	747.6
5°	738.4
7.5°	718.5
10°	691.7
12.5°	656.5
15°	616.0
17.5°	572.4
20°	529.5
22.5°	486.7
25°	441.5
27.5°	389.5
30°	329.8
32.5°	260.2
35°	191.3
37.5°	134.7
40°	91.8
42.5°	57.4
45°	33.7
47.5°	19.1
50°	9.9
52.5°	4.6
55°	3.1
57.5°	2.3
60°	2.3
62.5°	1.5
65°	1.5
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)