

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684821

Luminaire Tested: **LX6C130D010 EX61309030 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX61309030 6LBMLI
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12196.9 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684821

CATALOG NUMBER: LX6C130D010 EX61309030 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P684821

CATALOG NUMBER: LX6C130D010 EX61309030 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	836775
5°	828811
10°	785378
15°	713046
20°	630084
25°	544725
30°	425806
35°	261127
40°	134030
45°	53246
50°	17287
55°	5954
60°	5109
65°	4073
70°	2516
75°	3325
80°	0
85°	0



TEST NUMBER: P684821

CATALOG NUMBER: LX6C130D010 EX61309030 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1406.1	11.5
10°-20°	3500.8	28.7
20°-30°	4069.5	33.4
30°-40°	2492.0	20.4
40°-50°	618.8	5.1
50°-60°	72.3	0.6
60°-70°	27.0	0.2
70°-80°	10.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8976.5	73.6
0°-40°	11468.5	94.0
0°-60°	12159.6	99.7
0°-90°	12196.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12196.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15264	
5°	15061	###
15°	12564	3501
25°	9006	4070
35°	3902	2492
45°	687	619
55°	62	72
65°	31	27
75°	16	10
85°	0	0
90°	0	



TEST NUMBER: P684821

CATALOG NUMBER: LX6C130D010 EX61309030 6LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	15264.0
2.5°	15248.2
5°	15061.2
7.5°	14655.2
10°	14108.8
12.5°	13391.1
15°	12563.8
17.5°	11674.3
20°	10800.5
22.5°	9926.1
25°	9005.6
27.5°	7944.2
30°	6726.7
32.5°	5306.4
35°	3901.9
37.5°	2746.7
40°	1872.9
42.5°	1170.3
45°	686.8
47.5°	390.3
50°	202.7
52.5°	93.8
55°	62.3
57.5°	46.6
60°	46.6
62.5°	31.4
65°	31.4
67.5°	15.7
70°	15.7
72.5°	15.7
75°	15.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)