

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685051

Luminaire Tested: **LX6C05D010 EX6059035 6LRMDLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685051
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C05D010 EX6059035 6LRMDLI
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 509.0 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685051

CATALOG NUMBER: LX6C05D010 EX6059035 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P685051

CATALOG NUMBER: LX6C05D010 EX6059035 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41680
5°	41756
10°	39796
15°	34268
20°	28230
25°	22048
30°	15920
35°	8151
40°	3979
45°	1651
50°	298
55°	172
60°	110
65°	91
70°	64
75°	64
80°	32
85°	0



TEST NUMBER: P685051

CATALOG NUMBER: LX6C05D010 EX6059035 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.1	14.0
10°-20°	167.3	32.9
20°-30°	165.7	32.6
30°-40°	84.0	16.5
40°-50°	18.1	3.6
50°-60°	1.7	0.3
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.2	79.4
0°-40°	488.2	95.9
0°-60°	508.0	99.8
0°-90°	509.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	509.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	760	
5°	759	71
15°	604	167
25°	364	166
35°	122	84
45°	21	18
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P685051

CATALOG NUMBER: LX6C05D010 EX6059035 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	760.3
2.5°	761.2
5°	758.8
7.5°	746.9
10°	714.9
12.5°	663.4
15°	603.8
17.5°	542.7
20°	483.9
22.5°	425.0
25°	364.5
27.5°	302.8
30°	251.5
32.5°	193.8
35°	121.8
37.5°	82.0
40°	55.6
42.5°	36.0
45°	21.3
47.5°	9.5
50°	3.5
52.5°	2.4
55°	1.8
57.5°	1.3
60°	1.0
62.5°	0.8
65°	0.7
67.5°	0.5
70°	0.4
72.5°	0.3
75°	0.3
77.5°	0.1
80°	0.1
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)