

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684822

Luminaire Tested: **LX6C130D010 EX61309030 6LBNLI**

Issue Date: 2/14/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P684822  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX61309030 6LBNLI  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10839.0 lumens  
Efficiency: N/A  
Efficacy: 75.1 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684822  
CATALOG NUMBER: LX6C130D010 EX61309030 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684822

CATALOG NUMBER: LX6C130D010 EX61309030 6LBNI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1352841
5°	1265141
10°	1031817
15°	759284
20°	523342
25°	388528
30°	291842
35°	181991
40°	88344
45°	30305
50°	3974
55°	3011
60°	1721
65°	2037
70°	2516
75°	0
80°	0
85°	0



TEST NUMBER: P684822

CATALOG NUMBER: LX6C130D010 EX61309030 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2051.8	18.9
10°-20°	3682.8	34.0
20°-30°	2977.6	27.5
30°-40°	1715.3	15.8
40°-50°	362.6	3.3
50°-60°	31.3	0.3
60°-70°	15.6	0.1
70°-80°	2.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8712.2	80.4
0°-40°	10427.5	96.2
0°-60°	10821.4	99.8
0°-90°	10839.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10839.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	24678	
5°	22990	###
15°	13378	3683
25°	6423	2978
35°	2719	1715
45°	391	363
55°	32	31
65°	16	16
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P684822

CATALOG NUMBER: LX6C130D010 EX61309030 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	24677.8
2.5°	24381.3
5°	22990.2
7.5°	20989.6
10°	18535.9
12.5°	16019.8
15°	13378.5
17.5°	10831.0
20°	8970.8
22.5°	7548.8
25°	6423.3
27.5°	5470.2
30°	4610.4
32.5°	3657.3
35°	2719.4
37.5°	1891.0
40°	1234.5
42.5°	750.3
45°	390.9
47.5°	156.1
50°	46.6
52.5°	46.6
55°	31.5
57.5°	31.5
60°	15.7
62.5°	15.7
65°	15.7
67.5°	15.7
70°	15.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)