

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684825

Luminaire Tested: **LX6C130D010 EX61309030 6LRMDLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C130D010 EX61309030 6LRMDLI
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10230.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 144.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684825

CATALOG NUMBER: LX6C130D010 EX61309030 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P684825

CATALOG NUMBER: LX6C130D010 EX61309030 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | |
| 2 | 109 | 104 | 101 | 97 | 107 | 103 | 99 | 96 | 99 | 97 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 89 | | | |
| 3 | 104 | 98 | 93 | 90 | 102 | 97 | 92 | 89 | 94 | 90 | 87 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 83 | 89 | 85 | 82 | 87 | 83 | 81 | 85 | 82 | 80 | 78 | | | |
| 5 | 95 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 80 | 76 | 83 | 79 | 76 | 81 | 78 | 75 | 74 | | | |
| 6 | 90 | 82 | 77 | 73 | 89 | 81 | 76 | 72 | 80 | 75 | 72 | 79 | 74 | 71 | 77 | 74 | 71 | 70 | | | |
| 7 | 86 | 78 | 72 | 68 | 85 | 77 | 72 | 68 | 76 | 71 | 68 | 75 | 70 | 67 | 74 | 70 | 67 | 66 | | | |
| 8 | 83 | 74 | 68 | 64 | 81 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 64 | 70 | 66 | 63 | 62 | | | |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 64 | 61 | 69 | 64 | 61 | 68 | 63 | 60 | 67 | 63 | 60 | 59 | | | |
| 10 | 76 | 67 | 61 | 58 | 75 | 66 | 61 | 58 | 65 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 56 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 837641 |
| 5° | 839251 |
| 10° | 799807 |
| 15° | 688682 |
| 20° | 567335 |
| 25° | 443124 |
| 30° | 320024 |
| 35° | 163895 |
| 40° | 79914 |
| 45° | 33205 |
| 50° | 6047 |
| 55° | 3517 |
| 60° | 2302 |
| 65° | 1699 |
| 70° | 1266 |
| 75° | 1123 |
| 80° | 821 |
| 85° | 0 |



TEST NUMBER: P684825

CATALOG NUMBER: LX6C130D010 EX61309030 6LRMDLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1429.5 | 14.0 |
| 10°-20° | 3363.2 | 32.9 |
| 20°-30° | 3331.0 | 32.6 |
| 30°-40° | 1688.6 | 16.5 |
| 40°-50° | 363.8 | 3.6 |
| 50°-60° | 34.7 | 0.3 |
| 60°-70° | 13.3 | 0.1 |
| 70°-80° | 4.9 | 0.0 |
| 80°-90° | 1.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 8123.7 | 79.4 |
| 0°-40° | 9812.3 | 95.9 |
| 0°-60° | 10210.8 | 99.8 |
| 0°-90° | 10230.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 10230.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 15280 | |
| 5° | 15251 | ### |
| 15° | 12134 | 3363 |
| 25° | 7326 | 3331 |
| 35° | 2449 | 1689 |
| 45° | 428 | 364 |
| 55° | 37 | 35 |
| 65° | 13 | 13 |
| 75° | 5 | 5 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P684825

CATALOG NUMBER: LX6C130D010 EX61309030 6LRMDLI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 15279.8 |
| 2.5° | 15298.2 |
| 5° | 15250.9 |
| 7.5° | 15011.7 |
| 10° | 14368.0 |
| 12.5° | 13332.7 |
| 15° | 12134.5 |
| 17.5° | 10907.4 |
| 20° | 9724.9 |
| 22.5° | 8542.5 |
| 25° | 7325.9 |
| 27.5° | 6085.6 |
| 30° | 5055.6 |
| 32.5° | 3894.2 |
| 35° | 2449.0 |
| 37.5° | 1647.5 |
| 40° | 1116.7 |
| 42.5° | 722.6 |
| 45° | 428.3 |
| 47.5° | 191.8 |
| 50° | 70.9 |
| 52.5° | 47.3 |
| 55° | 36.8 |
| 57.5° | 26.3 |
| 60° | 21.0 |
| 62.5° | 15.8 |
| 65° | 13.1 |
| 67.5° | 10.5 |
| 70° | 7.9 |
| 72.5° | 5.3 |
| 75° | 5.3 |
| 77.5° | 2.6 |
| 80° | 2.6 |
| 82.5° | 2.6 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)