

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563958

Luminaire Tested: **LX6C05D010 EX6C059030 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C05D010 EX6C059030 6LBSH
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND
6LBS TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 695.9 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563958

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P563958

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19955
5°	19860
10°	19450
15°	18746
20°	17881
25°	16918
30°	15958
35°	15024
40°	14148
45°	13187
50°	12025
55°	10618
60°	8991
65°	7057
70°	5033
75°	2754
80°	474
85°	0



TEST NUMBER: P563958

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	4.9
10°-20°	92.7	13.3
20°-30°	128.7	18.5
30°-40°	140.4	20.2
40°-50°	131.0	18.8
50°-60°	99.4	14.3
60°-70°	54.4	7.8
70°-80°	15.0	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.5	36.7
0°-40°	395.9	56.9
0°-60°	626.3	90.0
0°-90°	695.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	364	
5°	361	34
15°	330	93
25°	280	129
35°	224	140
45°	170	131
55°	111	99
65°	54	54
75°	13	15
85°	0	0
90°	0	



TEST NUMBER: P563958

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	364.0
2.5°	364.0
5°	360.9
7.5°	356.3
10°	349.4
12.5°	340.2
15°	330.3
17.5°	318.0
20°	306.5
22.5°	292.7
25°	279.7
27.5°	266.7
30°	252.1
32.5°	238.3
35°	224.5
37.5°	210.7
40°	197.7
42.5°	183.9
45°	170.1
47.5°	156.3
50°	141.0
52.5°	126.4
55°	111.1
57.5°	96.6
60°	82.0
62.5°	67.4
65°	54.4
67.5°	42.1
70°	31.4
72.5°	21.5
75°	13.0
77.5°	6.1
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)