

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P683997

Luminaire Tested: **LX6C130D010 EX6C1309030 6LBMH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P683997  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX6C1309030 6LBMH  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9965.9 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P683997

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P683997

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	540686
5°	531002
10°	503876
15°	472500
20°	440041
25°	405459
30°	337837
35°	238112
40°	151749
45°	90498
50°	53414
55°	33987
60°	23408
65°	16617
70°	11428
75°	9044
80°	4420
85°	0



TEST NUMBER: P683997

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	901.8	9.0
10°-20°	2332.9	23.4
20°-30°	3022.8	30.3
30°-40°	2244.2	22.5
40°-50°	947.4	9.5
50°-60°	336.4	3.4
60°-70°	129.8	1.3
70°-80°	44.9	0.5
80°-90°	5.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6257.5	62.8
0°-40°	8501.7	85.3
0°-60°	9785.5	98.2
0°-90°	9965.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9965.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9863	
5°	9649	902
15°	8325	2333
25°	6703	3023
35°	3558	2244
45°	1167	947
55°	356	336
65°	128	130
75°	43	45
85°	0	6
90°	0	



TEST NUMBER: P683997

CATALOG NUMBER: LX6C130D010 EX6C1309030 6LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9862.9
2.5°	9834.3
5°	9649.4
7.5°	9378.7
10°	9051.8
12.5°	8695.6
15°	8325.4
17.5°	7913.1
20°	7542.9
22.5°	7158.7
25°	6703.2
27.5°	6076.8
30°	5337.0
32.5°	4468.6
35°	3558.0
37.5°	2789.6
40°	2120.5
42.5°	1579.6
45°	1167.3
47.5°	853.8
50°	626.3
52.5°	469.6
55°	355.6
57.5°	270.2
60°	213.5
62.5°	156.7
65°	128.1
67.5°	99.4
70°	71.3
72.5°	56.7
75°	42.7
77.5°	28.6
80°	14.0
82.5°	14.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)