

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685073

Luminaire Tested: **LX6C50D010 EX6509035 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P685073
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6509035 6LBNLI
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4349.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685073

CATALOG NUMBER: LX6C50D010 EX6509035 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685073

CATALOG NUMBER: LX6C50D010 EX6509035 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542807
5°	507620
10°	414004
15°	304650
20°	209983
25°	155894
30°	117100
35°	73020
40°	35445
45°	12156
50°	1595
55°	1204
60°	691
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P685073

CATALOG NUMBER: LX6C50D010 EX6509035 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	823.2	18.9
10°-20°	1477.7	34.0
20°-30°	1194.7	27.5
30°-40°	688.2	15.8
40°-50°	145.5	3.3
50°-60°	12.5	0.3
60°-70°	6.3	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3495.7	80.4
0°-40°	4183.9	96.2
0°-60°	4341.9	99.8
0°-90°	4349.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4349.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9902	
5°	9224	823
15°	5368	1478
25°	2577	1195
35°	1091	688
45°	157	145
55°	13	13
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685073

CATALOG NUMBER: LX6C50D010 EX6509035 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9901.6
2.5°	9782.7
5°	9224.5
7.5°	8421.8
10°	7437.3
12.5°	6427.7
15°	5367.9
17.5°	4345.8
20°	3599.4
22.5°	3028.9
25°	2577.3
27.5°	2194.9
30°	1849.9
32.5°	1467.4
35°	1091.1
37.5°	758.7
40°	495.3
42.5°	301.1
45°	156.8
47.5°	62.6
50°	18.7
52.5°	18.7
55°	12.6
57.5°	12.6
60°	6.3
62.5°	6.3
65°	6.3
67.5°	6.3
70°	6.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)