

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685078

Luminaire Tested: **LX6C50D010 EX6509040 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P685078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6509040 6LBNLI
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4355.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685078

CATALOG NUMBER: LX6C50D010 EX6509040 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685078

CATALOG NUMBER: LX6C50D010 EX6509040 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72		
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	543558
5°	508319
10°	414571
15°	305070
20°	210275
25°	156106
30°	117259
35°	73120
40°	35495
45°	12180
50°	1595
55°	1204
60°	691
65°	817
70°	1010
75°	0
80°	0
85°	0



TEST NUMBER: P685078

CATALOG NUMBER: LX6C50D010 EX6509040 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	824.4	18.9
10°-20°	1479.7	34.0
20°-30°	1196.4	27.5
30°-40°	689.2	15.8
40°-50°	145.7	3.3
50°-60°	12.5	0.3
60°-70°	6.3	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3500.5	80.4
0°-40°	4189.6	96.2
0°-60°	4347.9	99.8
0°-90°	4355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9915	
5°	9237	824
15°	5375	1480
25°	2581	1196
35°	1093	689
45°	157	146
55°	13	13
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685078

CATALOG NUMBER: LX6C50D010 EX6509040 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9915.3
2.5°	9796.2
5°	9237.2
7.5°	8433.4
10°	7447.5
12.5°	6436.6
15°	5375.3
17.5°	4351.8
20°	3604.4
22.5°	3033.0
25°	2580.8
27.5°	2197.9
30°	1852.4
32.5°	1469.5
35°	1092.6
37.5°	759.8
40°	496.0
42.5°	301.5
45°	157.1
47.5°	62.7
50°	18.7
52.5°	18.7
55°	12.6
57.5°	12.6
60°	6.3
62.5°	6.3
65°	6.3
67.5°	6.3
70°	6.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)