

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685085

Luminaire Tested: **LX6C50D010 EX6509050 6LCSWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P685085  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P252180)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C50D010 EX6509050 6LCSWLI  
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LCSW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5718.0 lumens  
Efficiency: N/A  
Efficacy: 97.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.29 / 1.21  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 58.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	103	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	105	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80																			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72																			
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65																			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58																			
6	80	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53																			
7	74	63	56	51	73	62	55	50	61	55	50	60	54	50	58	53	50	48																			
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44																			
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40																			
10	62	50	43	39	61	50	43	39	49	43	39	48	43	39	47	42	38	37																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	171488	171488	171488
5°	167042	172144	181196
10°	162979	178626	194446
15°	161074	187379	207578
20°	158762	192266	214592
25°	155392	190844	210744
30°	147662	181363	198398
35°	135098	163513	177125
40°	116855	135039	145315
45°	98545	88575	95056
50°	83665	51265	48212
55°	72600	24582	18570
60°	65576	11468	4583
65°	63613	6590	1544
70°	57045	5273	1443
75°	46873	3813	635
80°	34916	1894	0
85°	30129	0	0



TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	302.2	5.3
10°-20°	920.9	16.1
20°-30°	1407.0	24.6
30°-40°	1471.6	25.7
40°-50°	954.6	16.7
50°-60°	379.0	6.6
60°-70°	179.8	3.1
70°-80°	85.5	1.5
80°-90°	17.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2630.0	46.0
0°-40°	4101.6	71.7
0°-60°	5435.2	95.1
0°-90°	5718.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5718.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	3128	3128	3128	3128	3128	
5°	3036	3062	3128	3206	3293	287
15°	2838	2976	3302	3508	3658	800
25°	2569	2730	3155	3367	3484	1176
35°	2019	2141	2443	2587	2647	1248
45°	1271	1259	1142	1211	1226	989
55°	760	646	257	200	194	688
65°	490	407	51	12	12	479
75°	221	179	18	6	3	239
85°	48	30	0	0	0	56
90°	0	0	0	0	0	



TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2
2.5°	3089.3	3095.3	3062.4	3053.5	3077.4	3086.3	3089.3	3080.3	3083.4	3095.3	3095.3
5°	3035.5	3041.4	3011.5	3002.5	3026.5	3032.6	3041.4	3038.5	3047.5	3065.4	3062.4
7.5°	2984.7	2993.7	2960.7	2948.8	2978.7	2993.7	2999.6	2999.6	3011.5	3035.5	3038.5
10°	2927.8	2939.8	2909.9	2903.8	2936.8	2951.7	2954.8	2960.7	2978.7	3011.5	3017.5
12.5°	2880.0	2891.9	2871.0	2862.0	2897.9	2912.8	2918.8	2930.8	2951.7	2993.7	2999.6
15°	2838.1	2847.1	2823.1	2817.2	2853.0	2871.0	2873.9	2891.9	2918.8	2966.7	2975.7
17.5°	2784.2	2790.2	2772.3	2766.4	2802.2	2820.1	2823.1	2844.0	2877.0	2924.9	2939.8
20°	2721.4	2727.5	2709.5	2703.5	2739.4	2760.3	2763.3	2781.3	2820.1	2871.0	2886.0
22.5°	2646.7	2658.7	2637.8	2631.7	2667.7	2685.6	2694.6	2709.5	2748.4	2799.2	2820.1
25°	2569.0	2569.0	2554.0	2551.0	2583.9	2604.9	2601.8	2622.7	2661.6	2712.5	2730.4
27.5°	2467.3	2464.2	2449.3	2446.4	2482.2	2500.2	2494.1	2515.2	2551.0	2601.8	2619.8
30°	2332.7	2338.7	2317.8	2311.7	2341.7	2371.6	2368.6	2389.5	2425.3	2473.2	2485.3
32.5°	2171.2	2177.2	2174.2	2165.2	2192.1	2207.1	2216.0	2231.0	2260.9	2311.7	2323.7
35°	2018.7	2009.7	1997.8	1997.8	2024.6	2048.6	2039.6	2057.6	2087.5	2138.3	2141.3
37.5°	1830.3	1827.2	1821.3	1815.3	1845.2	1851.2	1854.2	1866.1	1893.1	1934.9	1929.0
40°	1632.9	1635.8	1632.9	1620.9	1638.9	1662.8	1659.8	1665.8	1689.7	1719.6	1710.7
42.5°	1447.4	1447.4	1447.4	1435.5	1456.4	1468.4	1474.4	1471.4	1477.3	1504.3	1492.3
45°	1271.1	1274.0	1271.1	1268.0	1271.1	1277.0	1271.1	1268.0	1268.0	1277.0	1259.0
47.5°	1118.5	1118.5	1109.5	1100.5	1109.5	1112.5	1103.6	1094.6	1091.6	1088.6	1058.7
50°	981.0	977.9	975.0	960.0	968.9	972.0	960.0	954.0	942.1	927.1	891.3
52.5°	861.4	858.3	855.3	840.3	846.4	849.3	837.4	825.4	810.4	798.5	753.7
55°	759.6	756.6	756.6	747.7	741.6	747.7	735.7	726.7	705.8	690.8	646.0
57.5°	672.9	672.9	666.9	657.9	660.9	660.9	649.0	637.0	619.0	601.1	565.3
60°	598.1	598.1	598.1	589.1	589.1	589.1	583.2	571.2	556.3	538.3	502.4
62.5°	538.3	538.3	535.3	526.4	529.3	529.3	523.4	511.4	496.5	484.5	448.6
65°	490.4	490.4	490.4	481.5	481.5	484.5	478.5	466.6	454.6	439.6	406.7
67.5°	430.6	427.7	427.7	421.6	424.7	427.7	421.6	412.7	397.8	388.8	358.9
70°	355.9	358.9	361.8	352.9	355.9	355.9	352.9	344.0	335.0	326.0	299.1
72.5°	290.1	290.1	287.1	284.2	284.2	287.1	281.1	272.1	266.2	260.2	239.2
75°	221.3	218.3	221.3	215.4	215.4	215.4	209.3	206.4	203.3	194.3	179.4
77.5°	161.5	158.5	158.5	152.5	155.6	155.6	152.5	146.6	140.5	137.6	125.6
80°	110.6	110.6	110.6	107.7	107.7	104.6	104.6	101.7	95.7	92.7	86.8
82.5°	74.7	74.7	74.7	71.8	71.8	71.8	68.8	65.8	62.8	59.8	53.8
85°	47.9	47.9	47.9	44.8	44.8	44.8	41.8	41.8	38.9	35.9	29.9
87.5°	26.9	26.9	26.9	23.9	23.9	23.9	23.9	23.9	20.9	18.0	14.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2
2.5°	3116.2	3074.4	3101.2	3101.2	3092.3	3116.2	3131.2	3143.2	3140.1	3113.3	3110.2
5°	3092.3	3056.4	3086.3	3089.3	3080.3	3113.3	3134.2	3149.1	3152.1	3128.2	3131.2
7.5°	3074.4	3044.5	3083.4	3095.3	3092.3	3122.2	3146.2	3170.0	3182.0	3164.1	3167.1
10°	3065.4	3041.4	3083.4	3101.2	3104.3	3137.2	3173.1	3206.0	3220.9	3208.9	3217.9
12.5°	3053.5	3038.5	3086.3	3113.3	3125.2	3158.1	3203.0	3241.8	3265.8	3259.8	3277.7
15°	3041.4	3029.5	3086.3	3125.2	3140.1	3170.0	3220.9	3277.7	3304.7	3301.6	3325.6
17.5°	3011.5	3008.6	3068.4	3110.2	3131.2	3167.1	3214.9	3283.7	3310.6	3316.6	3346.5
20°	2963.8	2963.8	3029.5	3074.4	3098.3	3131.2	3191.0	3256.8	3289.7	3295.7	3328.6
22.5°	2897.9	2903.8	2966.7	3011.5	3047.5	3071.3	3134.2	3203.0	3232.9	3241.8	3277.7
25°	2811.2	2817.2	2877.0	2921.8	2960.7	2987.6	3047.5	3110.2	3146.2	3155.1	3182.0
27.5°	2697.6	2709.5	2766.4	2811.2	2844.0	2862.0	2924.9	2990.6	3017.5	3026.5	3053.5
30°	2566.0	2569.0	2625.8	2664.7	2697.6	2712.5	2766.4	2835.2	2856.1	2865.1	2903.8
32.5°	2404.4	2401.5	2455.4	2491.2	2518.1	2536.1	2592.8	2637.8	2658.7	2673.6	2694.6
35°	2210.1	2207.1	2245.9	2287.9	2308.8	2314.7	2371.6	2419.4	2431.4	2443.3	2470.3
37.5°	1991.8	1991.8	2024.6	2045.6	2069.5	2078.5	2105.4	2159.3	2180.2	2177.2	2198.1
40°	1761.5	1749.6	1773.4	1794.4	1800.4	1803.3	1830.3	1872.1	1887.0	1887.0	1902.0
42.5°	1519.3	1501.3	1504.3	1516.2	1522.2	1501.3	1519.3	1546.1	1537.1	1549.2	1552.2
45°	1262.1	1235.1	1223.2	1196.2	1202.3	1181.3	1169.3	1175.3	1172.4	1142.5	1148.4
47.5°	1052.7	1004.9	983.9	945.1	936.1	912.2	897.2	870.2	846.4	846.4	831.3
50°	876.3	828.4	786.5	741.6	726.7	705.8	672.9	637.0	619.0	601.1	586.2
52.5°	735.7	684.9	634.0	586.2	565.3	538.3	493.5	457.6	424.7	406.7	388.8
55°	622.0	565.3	511.4	460.5	433.7	406.7	361.8	320.0	281.1	257.2	242.2
57.5°	535.3	481.5	424.7	370.8	346.9	317.0	269.2	224.2	188.4	161.5	146.6
60°	472.5	418.7	367.9	311.0	287.1	257.2	206.4	164.4	128.6	104.6	86.8
62.5°	418.7	370.8	317.0	266.2	242.2	212.3	164.4	122.6	89.7	65.8	50.8
65°	379.8	331.9	287.1	236.3	215.4	185.5	140.5	101.7	71.8	50.8	35.9
67.5°	335.0	293.0	248.2	206.4	185.5	161.5	119.6	86.8	59.8	41.8	29.9
70°	281.1	248.2	209.3	170.5	155.6	134.5	98.7	71.8	47.9	32.9	23.9
72.5°	224.2	197.4	167.5	137.6	125.6	104.6	80.7	56.9	35.9	23.9	18.0
75°	170.5	149.5	125.6	104.6	92.7	80.7	59.8	41.8	26.9	18.0	11.9
77.5°	116.7	107.7	89.7	71.8	65.8	56.9	38.9	26.9	18.0	11.9	6.0
80°	80.7	71.8	59.8	47.9	41.8	35.9	23.9	18.0	9.0	6.0	3.0
82.5°	50.8	41.8	35.9	29.9	26.9	20.9	14.9	9.0	6.0	3.0	3.0
85°	26.9	23.9	20.9	14.9	14.9	11.9	9.0	6.0	3.0	0.0	0.0
87.5°	14.9	11.9	9.0	6.0	6.0	3.0	3.0	3.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**CANDELA DISTRIBUTION (continued):**

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2
2.5°	3146.2	3146.2	3143.2	3179.0	3137.2	3179.0	3158.1	3179.0	3149.1	3146.2	3149.1
5°	3170.0	3179.0	3182.0	3214.9	3176.1	3226.9	3208.9	3226.9	3206.0	3211.9	3220.9
7.5°	3217.9	3232.9	3229.9	3271.7	3232.9	3289.7	3277.7	3304.7	3283.7	3289.7	3301.6
10°	3271.7	3289.7	3292.7	3334.6	3298.6	3367.4	3352.5	3382.4	3364.5	3373.5	3388.4
12.5°	3334.6	3355.5	3358.5	3406.3	3367.4	3439.2	3430.2	3460.1	3445.2	3454.2	3472.2
15°	3382.4	3412.3	3418.3	3466.1	3424.3	3499.0	3493.1	3532.0	3508.0	3523.0	3537.9
17.5°	3406.3	3433.3	3445.2	3490.0	3454.2	3528.9	3523.0	3555.9	3537.9	3552.9	3570.9
20°	3391.3	3424.3	3433.3	3478.1	3442.3	3517.0	3508.0	3541.0	3523.0	3534.9	3552.9
22.5°	3337.5	3370.4	3382.4	3424.3	3391.3	3460.1	3457.2	3487.1	3463.2	3478.1	3493.1
25°	3241.8	3277.7	3283.7	3322.6	3286.7	3358.5	3352.5	3385.4	3367.4	3376.4	3397.3
27.5°	3104.3	3146.2	3155.1	3188.0	3161.1	3220.9	3220.9	3247.8	3226.9	3226.9	3247.8
30°	2939.8	2981.6	2987.6	3014.6	2990.6	3044.5	3047.5	3074.4	3041.4	3059.4	3062.4
32.5°	2739.4	2766.4	2784.2	2808.2	2772.3	2841.1	2832.1	2853.0	2835.2	2835.2	2850.1
35°	2497.2	2530.1	2539.1	2569.0	2539.1	2592.8	2592.8	2604.9	2586.9	2586.9	2610.8
37.5°	2234.0	2258.0	2260.9	2290.8	2266.9	2311.7	2308.8	2317.8	2299.8	2311.7	2311.7
40°	1925.9	1943.9	1949.9	1964.8	1961.9	1994.7	1991.8	1997.8	1988.8	1991.8	1997.8
42.5°	1567.1	1591.0	1603.0	1614.9	1597.0	1641.9	1632.9	1641.9	1638.9	1641.9	1650.9
45°	1154.4	1172.4	1181.3	1184.3	1178.3	1205.2	1226.1	1208.2	1211.2	1205.2	1217.2
47.5°	834.4	837.4	831.3	849.3	834.4	846.4	852.4	855.3	837.4	834.4	846.4
50°	571.2	586.2	565.3	574.2	571.2	583.2	577.2	580.2	562.2	571.2	565.3
52.5°	379.8	376.8	370.8	373.9	367.9	367.9	367.9	373.9	361.8	355.9	349.9
55°	230.3	224.2	212.3	209.3	209.3	212.3	206.4	200.4	200.4	197.4	197.4
57.5°	134.5	125.6	119.6	116.7	110.6	107.7	104.6	104.6	98.7	98.7	98.7
60°	74.7	65.8	59.8	53.8	53.8	50.8	47.9	44.8	44.8	44.8	41.8
62.5°	38.9	32.9	26.9	23.9	23.9	20.9	18.0	18.0	18.0	18.0	14.9
65°	26.9	20.9	18.0	14.9	14.9	11.9	11.9	11.9	11.9	11.9	11.9
67.5°	20.9	18.0	14.9	11.9	11.9	11.9	9.0	9.0	9.0	9.0	9.0
70°	18.0	11.9	11.9	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
72.5°	11.9	11.9	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
75°	9.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0	6.0
77.5°	3.0	3.0	3.0	3.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0
80°	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





TEST NUMBER: P685085

CATALOG NUMBER: LX6C50D010 EX6509050 6LCSWLI

**CANDELA DISTRIBUTION (continued):**

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2	3128.2
2.5°	3176.1	3173.1	3176.1	3182.0	3170.0	3206.0	3188.0	3206.0
5°	3244.9	3247.8	3250.8	3259.8	3244.9	3289.7	3265.8	3292.7
7.5°	3334.6	3337.5	3340.5	3349.5	3340.5	3385.4	3358.5	3382.4
10°	3427.3	3433.3	3433.3	3448.2	3439.2	3481.0	3463.2	3493.1
12.5°	3514.0	3519.9	3526.0	3534.9	3528.9	3573.8	3558.8	3582.8
15°	3582.8	3594.7	3597.7	3609.6	3603.7	3651.6	3633.6	3657.5
17.5°	3615.7	3627.6	3627.6	3642.6	3636.6	3687.4	3663.5	3690.5
20°	3597.7	3606.7	3609.6	3624.7	3618.6	3669.5	3645.6	3678.4
22.5°	3541.0	3543.9	3546.9	3561.9	3558.8	3603.7	3582.8	3603.7
25°	3436.2	3445.2	3442.3	3454.2	3454.2	3490.0	3466.1	3484.1
27.5°	3286.7	3295.7	3295.7	3310.6	3298.6	3334.6	3310.6	3337.5
30°	3104.3	3113.3	3107.3	3119.2	3107.3	3143.2	3125.2	3134.2
32.5°	2886.0	2886.0	2888.9	2891.9	2886.0	2918.8	2900.9	2918.8
35°	2625.8	2631.7	2634.8	2637.8	2631.7	2655.7	2634.8	2646.7
37.5°	2332.7	2347.7	2344.6	2347.7	2338.7	2368.6	2350.6	2356.7
40°	2018.7	2018.7	2015.6	2021.7	2012.7	2036.7	2024.6	2030.6
42.5°	1653.8	1662.8	1650.9	1665.8	1641.9	1674.7	1662.8	1653.8
45°	1241.2	1229.1	1226.1	1229.1	1220.1	1223.2	1232.2	1226.1
47.5°	846.4	846.4	840.3	831.3	843.4	846.4	834.4	834.4
50°	568.2	568.2	562.2	559.2	565.3	562.2	556.3	565.3
52.5°	361.8	349.9	349.9	355.9	349.9	344.0	352.9	346.9
55°	197.4	191.4	191.4	197.4	191.4	191.4	188.4	194.3
57.5°	95.7	98.7	95.7	95.7	95.7	95.7	92.7	95.7
60°	41.8	41.8	41.8	41.8	41.8	41.8	41.8	41.8
62.5°	18.0	18.0	14.9	14.9	14.9	14.9	14.9	14.9
65°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
67.5°	9.0	9.0	9.0	9.0	9.0	11.9	9.0	9.0
70°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
72.5°	9.0	9.0	11.9	11.9	11.9	11.9	11.9	11.9
75°	6.0	6.0	6.0	3.0	3.0	3.0	3.0	3.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°    - - 45°-225°    - - - - 90°-270°















(END OF REPORT)