

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684025

Luminaire Tested: **LX6C130D010 EX6C1309050 6LBWH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684025  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C130D010 EX6C1309050 6LBWH  
Description: 6 INCH 13000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12500.0 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 144.3  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684025

CATALOG NUMBER: LX6C130D010 EX6C1309050 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P684025

CATALOG NUMBER: LX6C130D010 EX6C1309050 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	422636
5°	422490
10°	419242
15°	416433
20°	410090
25°	400717
30°	377305
35°	341455
40°	285127
45°	218480
50°	154733
55°	97554
60°	55028
65°	35724
70°	23337
75°	17135
80°	10292
85°	10253



TEST NUMBER: P684025

CATALOG NUMBER: LX6C130D010 EX6C1309050 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	728.2	5.8
10°-20°	2066.2	16.5
20°-30°	3029.5	24.2
30°-40°	3153.0	25.2
40°-50°	2181.4	17.5
50°-60°	949.8	7.6
60°-70°	291.3	2.3
70°-80°	87.3	0.7
80°-90°	13.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5823.9	46.6
0°-40°	8976.9	71.8
0°-60°	12108.1	96.9
0°-90°	12500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12500.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7710	
5°	7678	728
15°	7338	2066
25°	6625	3030
35°	5102	3153
45°	2818	2181
55°	1021	950
65°	275	291
75°	81	87
85°	16	13
90°	0	



TEST NUMBER: P684025

CATALOG NUMBER: LX6C130D010 EX6C1309050 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7709.5
2.5°	7725.8
5°	7677.5
7.5°	7612.9
10°	7531.4
12.5°	7450.4
15°	7337.5
17.5°	7191.3
20°	7029.5
22.5°	6851.3
25°	6624.8
27.5°	6333.1
30°	5960.5
32.5°	5571.5
35°	5102.2
37.5°	4584.0
40°	3984.3
42.5°	3385.2
45°	2818.1
47.5°	2283.6
50°	1814.3
52.5°	1377.0
55°	1020.7
57.5°	729.0
60°	501.9
62.5°	372.6
65°	275.4
67.5°	210.8
70°	145.6
72.5°	113.5
75°	80.9
77.5°	48.3
80°	32.6
82.5°	16.3
85°	16.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)