

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563963

Luminaire Tested: **LX6C50D010 EX6C509030 6LBMH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6C509030 6LBMH
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4010.9 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563963

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P563963

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217598
5°	213707
10°	202785
15°	190160
20°	177092
25°	163177
30°	135964
35°	95827
40°	61072
45°	36415
50°	21500
55°	13677
60°	9429
65°	6693
70°	4600
75°	3643
80°	1799
85°	0



TEST NUMBER: P563963

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.9	9.0
10°-20°	938.9	23.4
20°-30°	1216.5	30.3
30°-40°	903.2	22.5
40°-50°	381.3	9.5
50°-60°	135.4	3.4
60°-70°	52.3	1.3
70°-80°	18.1	0.5
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2518.4	62.8
0°-40°	3421.5	85.3
0°-60°	3938.2	98.2
0°-90°	4010.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4010.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3969	
5°	3884	363
15°	3351	939
25°	2698	1217
35°	1432	903
45°	470	381
55°	143	135
65°	52	52
75°	17	18
85°	0	2
90°	0	



TEST NUMBER: P563963

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3969.3
2.5°	3957.8
5°	3883.5
7.5°	3774.4
10°	3642.9
12.5°	3499.6
15°	3350.6
17.5°	3184.6
20°	3035.6
22.5°	2881.0
25°	2697.7
27.5°	2445.7
30°	2147.9
32.5°	1798.4
35°	1431.9
37.5°	1122.7
40°	853.4
42.5°	635.8
45°	469.7
47.5°	343.6
50°	252.1
52.5°	189.0
55°	143.1
57.5°	108.7
60°	86.0
62.5°	63.1
65°	51.6
67.5°	40.0
70°	28.7
72.5°	22.8
75°	17.2
77.5°	11.5
80°	5.7
82.5°	5.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)