

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684850

Luminaire Tested: **LX6C15D010 EX6159030 6LBMLI**

Issue Date: 2/15/2022

**Test Information**


Test Method: LM-79-08  
Report Number: P684850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C15D010 EX6159030 6LBMLI  
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1412.0 lumens  
Efficiency: N/A  
Efficacy: 89.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684850  
CATALOG NUMBER: LX6C15D010 EX6159030 6LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684850

CATALOG NUMBER: LX6C15D010 EX6159030 6LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	96867
5°	95950
10°	90919
15°	82549
20°	72941
25°	63058
30°	49292
35°	30229
40°	15515
45°	6163
50°	2004
55°	688
60°	592
65°	467
70°	289
75°	381
80°	0
85°	0



TEST NUMBER: P684850

CATALOG NUMBER: LX6C15D010 EX6159030 6LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.8	11.5
10°-20°	405.3	28.7
20°-30°	471.1	33.4
30°-40°	288.5	20.4
40°-50°	71.6	5.1
50°-60°	8.4	0.6
60°-70°	3.1	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.2	73.6
0°-40°	1327.7	94.0
0°-60°	1407.7	99.7
0°-90°	1412.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1412.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1767	
5°	1744	163
15°	1454	405
25°	1042	471
35°	452	288
45°	80	72
55°	7	8
65°	4	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P684850

CATALOG NUMBER: LX6C15D010 EX6159030 6LBMLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1767.0
2.5°	1765.2
5°	1743.6
7.5°	1696.6
10°	1633.3
12.5°	1550.2
15°	1454.5
17.5°	1351.5
20°	1250.3
22.5°	1149.1
25°	1042.5
27.5°	919.7
30°	778.7
32.5°	614.3
35°	451.7
37.5°	318.0
40°	216.8
42.5°	135.5
45°	79.5
47.5°	45.2
50°	23.5
52.5°	10.9
55°	7.2
57.5°	5.4
60°	5.4
62.5°	3.6
65°	3.6
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)