

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563966

Luminaire Tested: **LX6C50D010 EX6C509030 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6C509030 6LBWH
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4854.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563966

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P563966

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164121
5°	164065
10°	162806
15°	161715
20°	159252
25°	155610
30°	146516
35°	132595
40°	110729
45°	84838
50°	60083
55°	37886
60°	21369
65°	13867
70°	9072
75°	6651
80°	3978
85°	3963



TEST NUMBER: P563966

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.8	5.8
10°-20°	802.4	16.5
20°-30°	1176.5	24.2
30°-40°	1224.4	25.2
40°-50°	847.1	17.5
50°-60°	368.8	7.6
60°-70°	113.1	2.3
70°-80°	33.9	0.7
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2261.6	46.6
0°-40°	3486.0	71.8
0°-60°	4701.9	96.9
0°-90°	4854.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4854.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2994	
5°	2981	283
15°	2849	802
25°	2573	1176
35°	1981	1224
45°	1094	847
55°	396	369
65°	107	113
75°	31	34
85°	6	5
90°	0	



TEST NUMBER: P563966

CATALOG NUMBER: LX6C50D010 EX6C509030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2993.8
2.5°	3000.1
5°	2981.4
7.5°	2956.3
10°	2924.7
12.5°	2893.2
15°	2849.4
17.5°	2792.6
20°	2729.8
22.5°	2660.6
25°	2572.6
27.5°	2459.3
30°	2314.6
32.5°	2163.6
35°	1981.3
37.5°	1780.1
40°	1547.3
42.5°	1314.5
45°	1094.3
47.5°	886.8
50°	704.5
52.5°	534.7
55°	396.4
57.5°	283.1
60°	194.9
62.5°	144.7
65°	106.9
67.5°	81.9
70°	56.6
72.5°	44.0
75°	31.4
77.5°	18.7
80°	12.6
82.5°	6.3
85°	6.3
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)