

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856601

Luminaire Tested: **LD6C15D010 EU6159040 6LBWLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P856601
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C15D010 EU6159040 6LBWLI
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1619.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856601

CATALOG NUMBER: LD6C15D010 EU6159040 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856601

CATALOG NUMBER: LD6C15D010 EU6159040 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55483
5°	55993
10°	57564
15°	59001
20°	59896
25°	58661
30°	54996
35°	49168
40°	39825
45°	26344
50°	13313
55°	5620
60°	1809
65°	713
70°	593
75°	381
80°	0
85°	0



TEST NUMBER: P856601

CATALOG NUMBER: LD6C15D010 EU6159040 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.6	6.0
10°-20°	293.5	18.1
20°-30°	442.4	27.3
30°-40°	452.8	28.0
40°-50°	263.8	16.3
50°-60°	60.6	3.7
60°-70°	7.5	0.5
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.4	51.4
0°-40°	1286.2	79.4
0°-60°	1610.6	99.4
0°-90°	1619.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1619.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1012	
5°	1018	98
15°	1040	293
25°	970	442
35°	735	453
45°	340	264
55°	59	61
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P856601

CATALOG NUMBER: LD6C15D010 EU6159040 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1012.1
2.5°	1010.2
5°	1017.5
7.5°	1024.9
10°	1034.1
12.5°	1035.9
15°	1039.6
17.5°	1035.9
20°	1026.7
22.5°	997.3
25°	969.8
27.5°	925.7
30°	868.8
32.5°	810.0
35°	734.7
37.5°	650.2
40°	556.5
42.5°	451.8
45°	339.8
47.5°	236.9
50°	156.1
52.5°	99.2
55°	58.8
57.5°	31.2
60°	16.5
62.5°	9.2
65°	5.5
67.5°	5.5
70°	3.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)