

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684072

Luminaire Tested: **LX6C15D010 EX6C159040 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C15D010 EX6C159040 6LBSH
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1670.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684072

CATALOG NUMBER: LX6C15D010 EX6C159040 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684072

CATALOG NUMBER: LX6C15D010 EX6C159040 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47880
5°	47656
10°	46676
15°	44978
20°	42908
25°	40593
30°	38291
35°	36058
40°	33949
45°	31647
50°	28852
55°	25481
60°	21566
65°	16941
70°	12085
75°	6630
80°	1168
85°	0



TEST NUMBER: P684072

CATALOG NUMBER: LX6C15D010 EX6C159040 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.8	4.9
10°-20°	222.4	13.3
20°-30°	308.8	18.5
30°-40°	337.0	20.2
40°-50°	314.3	18.8
50°-60°	238.6	14.3
60°-70°	130.6	7.8
70°-80°	36.0	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.0	36.7
0°-40°	950.0	56.9
0°-60°	1502.9	90.0
0°-90°	1670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1670.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	873	
5°	866	82
15°	792	222
25°	671	309
35°	539	337
45°	408	314
55°	267	239
65°	131	131
75°	31	36
85°	0	1
90°	0	



TEST NUMBER: P684072

CATALOG NUMBER: LX6C15D010 EX6C159040 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	873.4
2.5°	873.4
5°	866.0
7.5°	855.0
10°	838.5
12.5°	816.4
15°	792.5
17.5°	763.1
20°	735.5
22.5°	702.4
25°	671.1
27.5°	639.9
30°	604.9
32.5°	571.8
35°	538.8
37.5°	505.7
40°	474.4
42.5°	441.3
45°	408.2
47.5°	375.1
50°	338.3
52.5°	303.4
55°	266.6
57.5°	231.7
60°	196.7
62.5°	161.8
65°	130.6
67.5°	101.1
70°	75.4
72.5°	51.5
75°	31.3
77.5°	14.7
80°	3.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)