

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684412

Luminaire Tested: **LX6C55D010 EX6C559030 6LBMDH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684412  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C55D010 EX6C559030 6LBMDH  
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4361.0 lumens  
Efficiency: N/A  
Efficacy: 68.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684412

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P684412

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	314224
5°	304501
10°	280394
15°	251494
20°	223769
25°	185823
30°	132761
35°	85340
40°	52005
45°	28910
50°	12810
55°	7417
60°	4879
65°	3463
70°	2452
75°	1885
80°	1200
85°	818



TEST NUMBER: P684412

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	512.2	11.7
10°-20°	1239.8	28.4
20°-30°	1378.7	31.6
30°-40°	817.0	18.7
40°-50°	299.3	6.9
50°-60°	75.2	1.7
60°-70°	27.5	0.6
70°-80°	9.6	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3130.7	71.8
0°-40°	3947.6	90.5
0°-60°	4322.1	99.1
0°-90°	4361.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4361.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5732	
5°	5533	512
15°	4431	1240
25°	3072	1379
35°	1275	817
45°	373	299
55°	78	75
65°	27	27
75°	9	10
85°	1	2
90°	0	



TEST NUMBER: P684412

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5731.9
2.5°	5681.0
5°	5533.4
7.5°	5309.4
10°	5037.1
12.5°	4736.7
15°	4431.3
17.5°	4134.8
20°	3835.7
22.5°	3488.3
25°	3072.1
27.5°	2593.6
30°	2097.3
32.5°	1653.1
35°	1275.2
37.5°	968.5
40°	726.7
42.5°	529.4
45°	372.9
47.5°	236.7
50°	150.2
52.5°	105.6
55°	77.6
57.5°	58.5
60°	44.5
62.5°	34.4
65°	26.7
67.5°	20.4
70°	15.3
72.5°	11.5
75°	8.9
77.5°	6.4
80°	3.8
82.5°	2.5
85°	1.3
87.5°	1.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)