

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684080

Luminaire Tested: **LX6C15D010 EX6C159050 6LBMDH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684080  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C15D010 EX6C159050 6LBMDH  
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1182.9 lumens  
Efficiency: N/A  
Efficacy: 74.9 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684080

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P684080

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 93  |    |    |   |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 94  | 98  | 95  | 92  | 95  | 93  | 90  | 92  | 90  | 89  | 87  |    |    |   |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  | 90  | 86  | 84  | 87  | 85  | 82  | 81  |    |    |   |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 80  | 86  | 82  | 79  | 84  | 81  | 78  | 83  | 79  | 77  | 75  |    |    |   |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |   |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 69  | 77  | 72  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 66  |    |    |   |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 63  | 70  | 66  | 63  | 62  |    |    |   |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 59  | 66  | 62  | 59  | 58  |    |    |   |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 54  |    |    |   |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 85240 |
| 5°  | 82599 |
| 10° | 76062 |
| 15° | 68224 |
| 20° | 60701 |
| 25° | 50410 |
| 30° | 36012 |
| 35° | 23149 |
| 40° | 14105 |
| 45° | 7846  |
| 50° | 3471  |
| 55° | 2017  |
| 60° | 1327  |
| 65° | 934   |
| 70° | 657   |
| 75° | 508   |
| 80° | 316   |
| 85° | 189   |



TEST NUMBER: P684080

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBMDH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 138.9  | 11.7      |
| 10°-20°   | 336.3  | 28.4      |
| 20°-30°   | 374.0  | 31.6      |
| 30°-40°   | 221.6  | 18.7      |
| 40°-50°   | 81.2   | 6.9       |
| 50°-60°   | 20.4   | 1.7       |
| 60°-70°   | 7.4    | 0.6       |
| 70°-80°   | 2.6    | 0.2       |
| 80°-90°   | 0.5    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 849.3  | 71.8      |
| 0°-40°    | 1070.9 | 90.5      |
| 0°-60°    | 1172.5 | 99.1      |
| 0°-90°    | 1182.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1182.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1555 |      |
| 5°  | 1501 | 139  |
| 15° | 1202 | 336  |
| 25° | 833  | 374  |
| 35° | 346  | 222  |
| 45° | 101  | 81   |
| 55° | 21   | 20   |
| 65° | 7    | 7    |
| 75° | 2    | 3    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P684080

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1554.9 |
| 2.5°  | 1541.1 |
| 5°    | 1501.0 |
| 7.5°  | 1440.3 |
| 10°   | 1366.4 |
| 12.5° | 1284.9 |
| 15°   | 1202.1 |
| 17.5° | 1121.6 |
| 20°   | 1040.5 |
| 22.5° | 946.3  |
| 25°   | 833.4  |
| 27.5° | 703.6  |
| 30°   | 568.9  |
| 32.5° | 448.4  |
| 35°   | 345.9  |
| 37.5° | 262.7  |
| 40°   | 197.1  |
| 42.5° | 143.6  |
| 45°   | 101.2  |
| 47.5° | 64.2   |
| 50°   | 40.7   |
| 52.5° | 28.7   |
| 55°   | 21.1   |
| 57.5° | 15.9   |
| 60°   | 12.1   |
| 62.5° | 9.3    |
| 65°   | 7.2    |
| 67.5° | 5.5    |
| 70°   | 4.1    |
| 72.5° | 3.1    |
| 75°   | 2.4    |
| 77.5° | 1.7    |
| 80°   | 1.0    |
| 82.5° | 0.7    |
| 85°   | 0.3    |
| 87.5° | 0.3    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)