

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684083

Luminaire Tested: **LX6C15D010 EX6C159050 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684083  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C15D010 EX6C159050 6LBSH  
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1704.0 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684083

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684083

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	48856
5°	48630
10°	47622
15°	45891
20°	43783
25°	41422
30°	39069
35°	36788
40°	34643
45°	32290
50°	29440
55°	26006
60°	22005
65°	17278
70°	12326
75°	6757
80°	1200
85°	0



TEST NUMBER: P684083

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.5	4.9
10°-20°	226.9	13.3
20°-30°	315.1	18.5
30°-40°	343.8	20.2
40°-50°	320.7	18.8
50°-60°	243.5	14.3
60°-70°	133.3	7.8
70°-80°	36.7	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.4	36.7
0°-40°	969.3	56.9
0°-60°	1533.5	90.0
0°-90°	1704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1704.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	891	
5°	884	83
15°	809	227
25°	685	315
35°	550	344
45°	416	321
55°	272	243
65°	133	133
75°	32	37
85°	0	1
90°	0	



TEST NUMBER: P684083

CATALOG NUMBER: LX6C15D010 EX6C159050 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	891.2
2.5°	891.2
5°	883.7
7.5°	872.4
10°	855.5
12.5°	833.0
15°	808.6
17.5°	778.6
20°	750.5
22.5°	716.7
25°	684.8
27.5°	652.9
30°	617.2
32.5°	583.5
35°	549.7
37.5°	516.0
40°	484.1
42.5°	450.3
45°	416.5
47.5°	382.7
50°	345.2
52.5°	309.6
55°	272.1
57.5°	236.4
60°	200.7
62.5°	165.1
65°	133.2
67.5°	103.2
70°	76.9
72.5°	52.5
75°	31.9
77.5°	15.0
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)