

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563909

Luminaire Tested: **LX6C15D010 EX6C159030 6LBSH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P563909  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C15D010 EX6C159030 6LBSH  
Description: 6 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1672.2 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563909

CATALOG NUMBER: LX6C15D010 EX6C159030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P563909

CATALOG NUMBER: LX6C15D010 EX6C159030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	47946
5°	47722
10°	46737
15°	45034
20°	42966
25°	40654
30°	38341
35°	36105
40°	33992
45°	31685
50°	28895
55°	25519
60°	21599
65°	16954
70°	12101
75°	6630
80°	1168
85°	0



TEST NUMBER: P563909

CATALOG NUMBER: LX6C15D010 EX6C159030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.9	4.9
10°-20°	222.7	13.3
20°-30°	309.2	18.5
30°-40°	337.4	20.2
40°-50°	314.8	18.8
50°-60°	238.9	14.3
60°-70°	130.8	7.8
70°-80°	36.0	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.8	36.7
0°-40°	951.2	56.9
0°-60°	1504.9	90.0
0°-90°	1672.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1672.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	875	
5°	867	82
15°	794	223
25°	672	309
35°	540	337
45°	409	315
55°	267	239
65°	131	131
75°	31	36
85°	0	1
90°	0	



TEST NUMBER: P563909

CATALOG NUMBER: LX6C15D010 EX6C159030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	874.6
2.5°	874.6
5°	867.2
7.5°	856.2
10°	839.6
12.5°	817.5
15°	793.5
17.5°	764.1
20°	736.5
22.5°	703.4
25°	672.1
27.5°	640.7
30°	605.7
32.5°	572.6
35°	539.5
37.5°	506.4
40°	475.0
42.5°	441.9
45°	408.7
47.5°	375.7
50°	338.8
52.5°	303.8
55°	267.0
57.5°	232.0
60°	197.0
62.5°	162.0
65°	130.7
67.5°	101.2
70°	75.5
72.5°	51.6
75°	31.3
77.5°	14.7
80°	3.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)