

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856651

Luminaire Tested: **LD6C55D010 EU6559040 6LBWLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P856651
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C55D010 EU6559040 6LBWLI
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6188.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856651

CATALOG NUMBER: LD6C55D010 EU6559040 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856651

CATALOG NUMBER: LD6C55D010 EU6559040 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211924
5°	213883
10°	219869
15°	225370
20°	228792
25°	224063
30°	210070
35°	187813
40°	152128
45°	100631
50°	50864
55°	21457
60°	6918
65°	2711
70°	2260
75°	1504
80°	0
85°	0



TEST NUMBER: P856651

CATALOG NUMBER: LD6C55D010 EU6559040 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.9	6.0
10°-20°	1120.9	18.1
20°-30°	1689.7	27.3
30°-40°	1729.5	27.9
40°-50°	1007.6	16.3
50°-60°	231.5	3.7
60°-70°	28.4	0.5
70°-80°	7.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3183.6	51.4
0°-40°	4913.1	79.4
0°-60°	6152.1	99.4
0°-90°	6188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6188.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3866	
5°	3887	373
15°	3971	1121
25°	3704	1690
35°	2806	1729
45°	1298	1008
55°	224	232
65°	21	28
75°	7	7
85°	0	0
90°	0	



TEST NUMBER: P856651

CATALOG NUMBER: LD6C55D010 EU6559040 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3865.8
2.5°	3858.7
5°	3886.7
7.5°	3914.7
10°	3949.8
12.5°	3956.9
15°	3971.0
17.5°	3956.9
20°	3921.8
22.5°	3809.5
25°	3704.3
27.5°	3536.1
30°	3318.6
32.5°	3094.1
35°	2806.4
37.5°	2483.5
40°	2125.8
42.5°	1725.9
45°	1298.0
47.5°	905.0
50°	596.4
52.5°	378.9
55°	224.5
57.5°	119.3
60°	63.1
62.5°	35.1
65°	20.9
67.5°	20.9
70°	14.1
72.5°	7.1
75°	7.1
77.5°	7.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)