

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856652

Luminaire Tested: **LD6C55D010 EU6559050 6LBWLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P856652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C55D010 EU6559050 6LBWLI
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6315.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856652

CATALOG NUMBER: LD6C55D010 EU6559050 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856652

CATALOG NUMBER: LD6C55D010 EU6559050 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216271
5°	218275
10°	224384
15°	229996
20°	233488
25°	228666
30°	214381
35°	191668
40°	155248
45°	102701
50°	51904
55°	21896
60°	7061
65°	2776
70°	2308
75°	1525
80°	0
85°	0



TEST NUMBER: P856652

CATALOG NUMBER: LD6C55D010 EU6559050 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.6	6.0
10°-20°	1143.9	18.1
20°-30°	1724.4	27.3
30°-40°	1765.0	27.9
40°-50°	1028.2	16.3
50°-60°	236.3	3.7
60°-70°	29.0	0.5
70°-80°	7.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3248.9	51.4
0°-40°	5013.9	79.4
0°-60°	6278.4	99.4
0°-90°	6315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3945	
5°	3966	381
15°	4052	1144
25°	3780	1724
35°	2864	1765
45°	1325	1028
55°	229	236
65°	21	29
75°	7	8
85°	0	0
90°	0	



TEST NUMBER: P856652

CATALOG NUMBER: LD6C55D010 EU6559050 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3945.1
2.5°	3937.9
5°	3966.5
7.5°	3995.1
10°	4030.9
12.5°	4038.1
15°	4052.5
17.5°	4038.1
20°	4002.3
22.5°	3887.7
25°	3780.4
27.5°	3608.6
30°	3386.7
32.5°	3157.6
35°	2864.0
37.5°	2534.5
40°	2169.4
42.5°	1761.3
45°	1324.7
47.5°	923.5
50°	608.6
52.5°	386.7
55°	229.1
57.5°	121.8
60°	64.4
62.5°	35.8
65°	21.4
67.5°	21.4
70°	14.4
72.5°	7.2
75°	7.2
77.5°	7.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)