

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684127

Luminaire Tested: **LX6C20D010 EX6C209727 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C20D010 EX6C209727 6LBSH
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 97CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2040.0 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684127

CATALOG NUMBER: LX6C20D010 EX6C209727 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684127

CATALOG NUMBER: LX6C20D010 EX6C209727 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58488
5°	58216
10°	57013
15°	54944
20°	52417
25°	49588
30°	46779
35°	44042
40°	41471
45°	38655
50°	35248
55°	31129
60°	26347
65°	20690
70°	14762
75°	8091
80°	1421
85°	0



TEST NUMBER: P684127

CATALOG NUMBER: LX6C20D010 EX6C209727 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	4.9
10°-20°	271.6	13.3
20°-30°	377.2	18.5
30°-40°	411.6	20.2
40°-50°	384.0	18.8
50°-60°	291.5	14.3
60°-70°	159.6	7.8
70°-80°	43.9	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.8	36.7
0°-40°	1160.4	56.9
0°-60°	1835.9	90.0
0°-90°	2040.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2040.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1067	
5°	1058	100
15°	968	272
25°	820	377
35°	658	412
45°	499	384
55°	326	291
65°	160	160
75°	38	44
85°	0	1
90°	0	



TEST NUMBER: P684127

CATALOG NUMBER: LX6C20D010 EX6C209727 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1066.9
2.5°	1066.9
5°	1057.9
7.5°	1044.4
10°	1024.2
12.5°	997.3
15°	968.1
17.5°	932.1
20°	898.5
22.5°	858.0
25°	819.8
27.5°	781.7
30°	739.0
32.5°	698.5
35°	658.1
37.5°	617.7
40°	579.5
42.5°	539.1
45°	498.6
47.5°	458.2
50°	413.3
52.5°	370.6
55°	325.7
57.5°	283.0
60°	240.3
62.5°	197.7
65°	159.5
67.5°	123.5
70°	92.1
72.5°	62.9
75°	38.2
77.5°	18.0
80°	4.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)