

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684451

Luminaire Tested: **LX6C60D010 EX6C609030 6LBMDH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609030 6LBMDH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4714.1 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684451

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P684451

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	339660
5°	329148
10°	303089
15°	271852
20°	241883
25°	200866
30°	143509
35°	92247
40°	56212
45°	31251
50°	13842
55°	8019
60°	5274
65°	3749
70°	2645
75°	2033
80°	1294
85°	881



TEST NUMBER: P684451

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	553.7	11.7
10°-20°	1340.1	28.4
20°-30°	1490.3	31.6
30°-40°	883.1	18.7
40°-50°	323.5	6.9
50°-60°	81.3	1.7
60°-70°	29.7	0.6
70°-80°	10.3	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3384.1	71.8
0°-40°	4267.2	90.5
0°-60°	4672.0	99.1
0°-90°	4714.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4714.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6196	
5°	5981	554
15°	4790	1340
25°	3321	1490
35°	1378	883
45°	403	324
55°	84	81
65°	29	30
75°	10	10
85°	1	2
90°	0	



TEST NUMBER: P684451

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6195.9
2.5°	6140.9
5°	5981.3
7.5°	5739.2
10°	5444.8
12.5°	5120.1
15°	4790.0
17.5°	4469.4
20°	4146.2
22.5°	3770.6
25°	3320.8
27.5°	2803.6
30°	2267.1
32.5°	1787.0
35°	1378.4
37.5°	1046.9
40°	785.5
42.5°	572.3
45°	403.1
47.5°	255.9
50°	162.3
52.5°	114.2
55°	83.9
57.5°	63.3
60°	48.1
62.5°	37.1
65°	28.9
67.5°	22.0
70°	16.5
72.5°	12.4
75°	9.6
77.5°	6.9
80°	4.1
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)