

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563916

Luminaire Tested: **LX6C20D010 EX6C209030 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C20D010 EX6C209030 6LBSH
Description: 6 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2121.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563916

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P563916

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60812
5°	60527
10°	59279
15°	57123
20°	54494
25°	51559
30°	48634
35°	45795
40°	43116
45°	40190
50°	36647
55°	32362
60°	27399
65°	21507
70°	15355
75°	8409
80°	1484
85°	0



TEST NUMBER: P563916

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	4.9
10°-20°	282.4	13.3
20°-30°	392.2	18.5
30°-40°	428.0	20.2
40°-50°	399.2	18.8
50°-60°	303.0	14.3
60°-70°	165.9	7.8
70°-80°	45.7	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.5	36.7
0°-40°	1206.5	56.9
0°-60°	1908.8	90.0
0°-90°	2121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1109	
5°	1100	104
15°	1006	282
25°	852	392
35°	684	428
45°	518	399
55°	339	303
65°	166	166
75°	40	46
85°	0	1
90°	0	



TEST NUMBER: P563916

CATALOG NUMBER: LX6C20D010 EX6C209030 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1109.3
2.5°	1109.3
5°	1099.9
7.5°	1085.9
10°	1064.9
12.5°	1036.9
15°	1006.5
17.5°	969.1
20°	934.1
22.5°	892.1
25°	852.4
27.5°	812.7
30°	768.3
32.5°	726.3
35°	684.3
37.5°	642.2
40°	602.5
42.5°	560.5
45°	518.4
47.5°	476.4
50°	429.7
52.5°	385.3
55°	338.6
57.5°	294.3
60°	249.9
62.5°	205.5
65°	165.8
67.5°	128.4
70°	95.8
72.5°	65.4
75°	39.7
77.5°	18.7
80°	4.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)