

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684136

Luminaire Tested: **LX6C25D010 EX6C259027 6LBWH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684136
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C25D010 EX6C259027 6LBWH
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2176.0 lumens
Efficiency: N/A
Efficacy: 69.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684136

CATALOG NUMBER: LX6C25D010 EX6C259027 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P684136

CATALOG NUMBER: LX6C25D010 EX6C259027 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73574
5°	73547
10°	72984
15°	72492
20°	71389
25°	69754
30°	65681
35°	59441
40°	49636
45°	38035
50°	26933
55°	16984
60°	9583
65°	6213
70°	4055
75°	2987
80°	1799
85°	1761



TEST NUMBER: P684136

CATALOG NUMBER: LX6C25D010 EX6C259027 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	5.8
10°-20°	359.7	16.5
20°-30°	527.4	24.2
30°-40°	548.9	25.2
40°-50°	379.7	17.5
50°-60°	165.3	7.6
60°-70°	50.7	2.3
70°-80°	15.2	0.7
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.8	46.6
0°-40°	1562.7	71.8
0°-60°	2107.8	96.9
0°-90°	2176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2176.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1342	
5°	1336	127
15°	1277	360
25°	1153	527
35°	888	549
45°	491	380
55°	178	165
65°	48	51
75°	14	15
85°	3	2
90°	0	



TEST NUMBER: P684136

CATALOG NUMBER: LX6C25D010 EX6C259027 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1342.1
2.5°	1344.9
5°	1336.5
7.5°	1325.3
10°	1311.1
12.5°	1297.0
15°	1277.3
17.5°	1251.9
20°	1223.7
22.5°	1192.7
25°	1153.2
27.5°	1102.5
30°	1037.6
32.5°	969.9
35°	888.2
37.5°	798.0
40°	693.6
42.5°	589.3
45°	490.6
47.5°	397.5
50°	315.8
52.5°	239.7
55°	177.7
57.5°	126.9
60°	87.4
62.5°	64.9
65°	47.9
67.5°	36.7
70°	25.3
72.5°	19.8
75°	14.1
77.5°	8.4
80°	5.7
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)