

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685122

Luminaire Tested: **LX6C60D010 EX6609035 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685122
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6609035 6LBMLI
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5913.9 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685122

CATALOG NUMBER: LX6C60D010 EX6609035 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685122

CATALOG NUMBER: LX6C60D010 EX6609035 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98 | 98 | 97 | 96 | 94 | 94 | 94 | 94 |
| 2 | 108 | 103 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | 96 | 93 | 91 | 93 | 91 | 89 | 88 | 88 | 88 | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | 90 | 87 | 85 | 88 | 85 | 83 | 82 | 82 | 82 | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 89 | 84 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 83 | 80 | 78 | 76 | 76 | 76 | 76 |
| 5 | 93 | 85 | 79 | 75 | 91 | 84 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 73 | 79 | 76 | 73 | 71 | 71 | 71 | 71 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | 67 | 67 | 67 |
| 7 | 84 | 75 | 69 | 65 | 83 | 75 | 69 | 65 | 73 | 68 | 65 | 72 | 68 | 64 | 71 | 67 | 64 | 63 | 63 | 63 | 63 |
| 8 | 80 | 71 | 65 | 61 | 79 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 60 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |
| 9 | 77 | 67 | 61 | 57 | 75 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 55 | 55 | 55 | 55 |
| 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 62 | 57 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 52 | 52 | 52 | 52 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 405730 |
| 5° | 401870 |
| 10° | 380810 |
| 15° | 345740 |
| 20° | 305512 |
| 25° | 264124 |
| 30° | 206462 |
| 35° | 126612 |
| 40° | 64986 |
| 45° | 25817 |
| 50° | 8384 |
| 55° | 2886 |
| 60° | 2478 |
| 65° | 1972 |
| 70° | 1218 |
| 75° | 1610 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P685122

CATALOG NUMBER: LX6C60D010 EX6609035 6LBMLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 681.8 | 11.5 |
| 10°-20° | 1697.5 | 28.7 |
| 20°-30° | 1973.2 | 33.4 |
| 30°-40° | 1208.3 | 20.4 |
| 40°-50° | 300.0 | 5.1 |
| 50°-60° | 35.1 | 0.6 |
| 60°-70° | 13.1 | 0.2 |
| 70°-80° | 5.0 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4352.5 | 73.6 |
| 0°-40° | 5560.8 | 94.0 |
| 0°-60° | 5895.9 | 99.7 |
| 0°-90° | 5913.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5913.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7401 | |
| 5° | 7303 | 682 |
| 15° | 6092 | 1697 |
| 25° | 4367 | 1973 |
| 35° | 1892 | 1208 |
| 45° | 333 | 300 |
| 55° | 30 | 35 |
| 65° | 15 | 13 |
| 75° | 8 | 5 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P685122

CATALOG NUMBER: LX6C60D010 EX6609035 6LBMLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7401.1 |
| 2.5° | 7393.5 |
| 5° | 7302.8 |
| 7.5° | 7105.9 |
| 10° | 6841.0 |
| 12.5° | 6493.0 |
| 15° | 6091.9 |
| 17.5° | 5660.5 |
| 20° | 5236.9 |
| 22.5° | 4812.9 |
| 25° | 4366.6 |
| 27.5° | 3851.9 |
| 30° | 3261.6 |
| 32.5° | 2573.0 |
| 35° | 1891.9 |
| 37.5° | 1331.8 |
| 40° | 908.1 |
| 42.5° | 567.5 |
| 45° | 333.0 |
| 47.5° | 189.2 |
| 50° | 98.3 |
| 52.5° | 45.5 |
| 55° | 30.2 |
| 57.5° | 22.6 |
| 60° | 22.6 |
| 62.5° | 15.2 |
| 65° | 15.2 |
| 67.5° | 7.6 |
| 70° | 7.6 |
| 72.5° | 7.6 |
| 75° | 7.6 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)