

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P582996

Luminaire Tested: **LX6C60D010 EU6609040 6LBHYLI**

Issue Date: 8/31/2023



Test Information

Test Method: LM-79-08
Report Number: P582996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 8/31/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EU6609040 6LBHYLI
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LCHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4365.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P582996

CATALOG NUMBER: LX6C60D010 EU6609040 6LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P582996

CATALOG NUMBER: LX6C60D010 EU6609040 6LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71			
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	740237
5°	721548
10°	611740
15°	396501
20°	246235
25°	132528
30°	45551
35°	18344
40°	4902
45°	2186
50°	861
55°	382
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P582996

CATALOG NUMBER: LX6C60D010 EU6609040 6LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1182.7	27.1
10°-20°	1950.6	44.7
20°-30°	1011.3	23.2
30°-40°	191.5	4.4
40°-50°	24.2	0.6
50°-60°	3.5	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4144.5	95.0
0°-40°	4336.0	99.3
0°-60°	4363.7	100.0
0°-90°	4365.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4365.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13503	
5°	13112	###
15°	6986	1951
25°	2191	1011
35°	274	192
45°	28	24
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P582996

CATALOG NUMBER: LX6C60D010 EU6609040 6LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13503.0
2.5°	13480.8
5°	13112.0
7.5°	12265.4
10°	10989.5
12.5°	9068.5
15°	6986.3
17.5°	5305.3
20°	4220.8
22.5°	3146.5
25°	2191.0
27.5°	1346.5
30°	719.6
32.5°	485.8
35°	274.1
37.5°	118.9
40°	68.5
42.5°	44.3
45°	28.2
47.5°	16.1
50°	10.1
52.5°	4.0
55°	4.0
57.5°	2.0
60°	2.0
62.5°	2.0
65°	2.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)