

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684929

Luminaire Tested: **LX6C25D010 EX6259040 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C25D010 EX6259040 6LBSLI
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2800.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684929
CATALOG NUMBER: LX6C25D010 EX6259040 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684929

CATALOG NUMBER: LX6C25D010 EX6259040 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96862
5°	95762
10°	90908
15°	83905
20°	76703
25°	69452
30°	63269
35°	58531
40°	54710
45°	50967
50°	46429
55°	40658
60°	33912
65°	26618
70°	18593
75°	10082
80°	1894
85°	0



TEST NUMBER: P684929

CATALOG NUMBER: LX6C25D010 EX6259040 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.8	5.8
10°-20°	414.5	14.8
20°-30°	528.6	18.9
30°-40°	548.2	19.6
40°-50°	505.1	18.0
50°-60°	380.0	13.6
60°-70°	205.1	7.3
70°-80°	55.0	2.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.9	39.5
0°-40°	1654.1	59.1
0°-60°	2539.1	90.7
0°-90°	2800.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2800.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1767	
5°	1740	163
15°	1478	415
25°	1148	529
35°	875	548
45°	657	505
55°	425	380
65°	205	205
75°	48	55
85°	0	1
90°	0	



TEST NUMBER: P684929

CATALOG NUMBER: LX6C25D010 EX6259040 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1766.9
2.5°	1761.0
5°	1740.2
7.5°	1701.5
10°	1633.1
12.5°	1564.7
15°	1478.4
17.5°	1398.1
20°	1314.8
22.5°	1228.6
25°	1148.2
27.5°	1070.9
30°	999.5
32.5°	934.0
35°	874.6
37.5°	818.0
40°	764.5
42.5°	708.0
45°	657.4
47.5°	600.9
50°	544.4
52.5°	484.9
55°	425.4
57.5°	365.9
60°	309.3
62.5°	255.8
65°	205.2
67.5°	157.7
70°	116.0
72.5°	80.3
75°	47.6
77.5°	20.8
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)