

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684465

Luminaire Tested: **LX6C60D010 EX6C609040 6LBMDH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609040 6LBMDH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4788.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684465

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P684465

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344989
5°	334316
10°	307843
15°	276120
20°	245681
25°	204018
30°	145757
35°	93692
40°	57093
45°	31740
50°	14064
55°	8143
60°	5361
65°	3801
70°	2693
75°	2076
80°	1326
85°	881



TEST NUMBER: P684465

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	562.3	11.7
10°-20°	1361.2	28.4
20°-30°	1513.7	31.6
30°-40°	896.9	18.7
40°-50°	328.6	6.9
50°-60°	82.6	1.7
60°-70°	30.1	0.6
70°-80°	10.5	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3437.2	71.8
0°-40°	4334.1	90.5
0°-60°	4745.3	99.1
0°-90°	4788.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4788.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6293	
5°	6075	562
15°	4865	1361
25°	3373	1514
35°	1400	897
45°	409	329
55°	85	83
65°	29	30
75°	10	11
85°	1	2
90°	0	



TEST NUMBER: P684465

CATALOG NUMBER: LX6C60D010 EX6C609040 6LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6293.1
2.5°	6237.2
5°	6075.2
7.5°	5829.3
10°	5530.2
12.5°	5200.5
15°	4865.2
17.5°	4539.6
20°	4211.3
22.5°	3829.8
25°	3372.9
27.5°	2847.6
30°	2302.6
32.5°	1815.0
35°	1400.0
37.5°	1063.3
40°	797.8
42.5°	581.2
45°	409.4
47.5°	259.9
50°	164.9
52.5°	116.0
55°	85.2
57.5°	64.3
60°	48.9
62.5°	37.7
65°	29.3
67.5°	22.4
70°	16.8
72.5°	12.6
75°	9.8
77.5°	7.0
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)