

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856657

Luminaire Tested: **LD6C60D010 EU6609050 6LBWLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P856657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C60D010 EU6609050 6LBWLI
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6827.1 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P856657

CATALOG NUMBER: LD6C60D010 EU6609050 6LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P856657

CATALOG NUMBER: LD6C60D010 EU6609050 6LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	233808
5°	235972
10°	242575
15°	248645
20°	252419
25°	247206
30°	231764
35°	207214
40°	167836
45°	111027
50°	56118
55°	23674
60°	7631
65°	2996
70°	2500
75°	1652
80°	0
85°	0



TEST NUMBER: P856657

CATALOG NUMBER: LD6C60D010 EU6609050 6LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	411.4	6.0
10°-20°	1236.7	18.1
20°-30°	1864.2	27.3
30°-40°	1908.1	27.9
40°-50°	1111.6	16.3
50°-60°	255.5	3.7
60°-70°	31.4	0.5
70°-80°	8.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3512.3	51.4
0°-40°	5420.4	79.4
0°-60°	6787.5	99.4
0°-90°	6827.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6827.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4265	
5°	4288	411
15°	4381	1237
25°	4087	1864
35°	3096	1908
45°	1432	1112
55°	248	255
65°	23	31
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P856657

CATALOG NUMBER: LD6C60D010 EU6609050 6LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4265.0
2.5°	4257.2
5°	4288.1
7.5°	4319.0
10°	4357.7
12.5°	4365.5
15°	4381.1
17.5°	4365.5
20°	4326.8
22.5°	4202.9
25°	4086.9
27.5°	3901.2
30°	3661.3
32.5°	3413.6
35°	3096.3
37.5°	2740.0
40°	2345.3
42.5°	1904.1
45°	1432.1
47.5°	998.4
50°	658.0
52.5°	418.1
55°	247.7
57.5°	131.7
60°	69.6
62.5°	38.7
65°	23.1
67.5°	23.1
70°	15.6
72.5°	7.8
75°	7.8
77.5°	7.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)