

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563923

Luminaire Tested: **LX6C25D010 EX6C259030 6LBSH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P563923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C25D010 EX6C259030 6LBSH  
Description: 6 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2664.0 lumens  
Efficiency: N/A  
Efficacy: 84.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76381
5°	76023
10°	74453
15°	71748
20°	68448
25°	64758
30°	61085
35°	57514
40°	54159
45°	50486
50°	46028
55°	40648
60°	34405
65°	27020
70°	19282
75°	10569
80°	1863
85°	0



TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.5	4.9
10°-20°	354.7	13.3
20°-30°	492.6	18.5
30°-40°	537.5	20.2
40°-50°	501.5	18.8
50°-60°	380.6	14.3
60°-70°	208.4	7.8
70°-80°	57.4	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.8	36.7
0°-40°	1515.4	56.9
0°-60°	2397.5	90.0
0°-90°	2664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2664.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1393	
5°	1382	131
15°	1264	355
25°	1071	493
35°	859	538
45°	651	501
55°	425	381
65°	208	208
75°	50	57
85°	0	1
90°	0	



TEST NUMBER: P563923

CATALOG NUMBER: LX6C25D010 EX6C259030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1393.3
2.5°	1393.3
5°	1381.5
7.5°	1363.9
10°	1337.5
12.5°	1302.3
15°	1264.2
17.5°	1217.3
20°	1173.3
22.5°	1120.5
25°	1070.6
27.5°	1020.7
30°	965.0
32.5°	912.2
35°	859.4
37.5°	806.6
40°	756.8
42.5°	704.0
45°	651.2
47.5°	598.4
50°	539.7
52.5°	484.0
55°	425.3
57.5°	369.6
60°	313.8
62.5°	258.1
65°	208.3
67.5°	161.3
70°	120.3
72.5°	82.1
75°	49.9
77.5°	23.5
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)