

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684181

Luminaire Tested: **LX6C30D010 EX6C309030 6LBSH**

Issue Date: 2/15/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P684181  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C30D010 EX6C309030 6LBSH  
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3128.0 lumens  
Efficiency: N/A  
Efficacy: 99.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684181  
CATALOG NUMBER: LX6C30D010 EX6C309030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684181

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89680
5°	89263
10°	87423
15°	84246
20°	80367
25°	76039
30°	71726
35°	67532
40°	63591
45°	59277
50°	54045
55°	47731
60°	40402
65°	31728
70°	22632
75°	12391
80°	2178
85°	0



TEST NUMBER: P684181

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.2	4.9
10°-20°	416.5	13.3
20°-30°	578.4	18.5
30°-40°	631.2	20.2
40°-50°	588.8	18.8
50°-60°	446.9	14.3
60°-70°	244.7	7.8
70°-80°	67.3	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1148.1	36.7
0°-40°	1779.3	56.9
0°-60°	2815.0	90.0
0°-90°	3128.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3128.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1636	
5°	1622	153
15°	1484	416
25°	1257	578
35°	1009	631
45°	765	589
55°	499	447
65°	245	245
75°	58	67
85°	0	1
90°	0	



TEST NUMBER: P684181

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1635.9
2.5°	1635.9
5°	1622.1
7.5°	1601.4
10°	1570.5
12.5°	1529.1
15°	1484.4
17.5°	1429.3
20°	1377.6
22.5°	1315.6
25°	1257.1
27.5°	1198.5
30°	1133.1
32.5°	1071.1
35°	1009.1
37.5°	947.1
40°	888.6
42.5°	826.6
45°	764.6
47.5°	702.6
50°	633.7
52.5°	568.3
55°	499.4
57.5°	434.0
60°	368.5
62.5°	303.1
65°	244.6
67.5°	189.4
70°	141.2
72.5°	96.4
75°	58.5
77.5°	27.6
80°	6.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)