

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563980

Luminaire Tested: **LX6C60D010 EX6C609030 6LBWH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C60D010 EX6C609030 6LBWH
Description: 6 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5767.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563980

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P563980

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194990
5°	194920
10°	193422
15°	192124
20°	189197
25°	184874
30°	174071
35°	157537
40°	131546
45°	100793
50°	71384
55°	45007
60°	25393
65°	16487
70°	10771
75°	7900
80°	4735
85°	4717



TEST NUMBER: P563980

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.0	5.8
10°-20°	953.3	16.5
20°-30°	1397.7	24.2
30°-40°	1454.7	25.2
40°-50°	1006.4	17.5
50°-60°	438.2	7.6
60°-70°	134.4	2.3
70°-80°	40.3	0.7
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2686.9	46.6
0°-40°	4141.6	71.8
0°-60°	5586.2	96.9
0°-90°	5767.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5767.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3557	
5°	3542	336
15°	3385	953
25°	3056	1398
35°	2354	1455
45°	1300	1006
55°	471	438
65°	127	134
75°	37	40
85°	8	6
90°	0	



TEST NUMBER: P563980

CATALOG NUMBER: LX6C60D010 EX6C609030 6LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3556.9
2.5°	3564.4
5°	3542.1
7.5°	3512.3
10°	3474.7
12.5°	3437.3
15°	3385.2
17.5°	3317.8
20°	3243.1
22.5°	3160.9
25°	3056.4
27.5°	2921.8
30°	2749.9
32.5°	2570.5
35°	2354.0
37.5°	2114.9
40°	1838.2
42.5°	1561.8
45°	1300.1
47.5°	1053.6
50°	837.0
52.5°	635.3
55°	470.9
57.5°	336.3
60°	231.6
62.5°	171.9
65°	127.1
67.5°	97.2
70°	67.2
72.5°	52.4
75°	37.3
77.5°	22.3
80°	15.0
82.5°	7.5
85°	7.5
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)