

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856663

Luminaire Tested: **LD6C70D010 EU6709027 6LBWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856663  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C70D010 EU6709027 6LBWLI  
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6961.0 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856663

CATALOG NUMBER: LD6C70D010 EU6709027 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856663

CATALOG NUMBER: LD6C70D010 EU6709027 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92																			
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83																			
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76																			
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69																			
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63																			
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57																			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52																			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																			
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44																			
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	238396
5°	240606
10°	247335
15°	253526
20°	257372
25°	252057
30°	236309
35°	211276
40°	171128
45°	113206
50°	57218
55°	24143
60°	7784
65°	3061
70°	2549
75°	1673
80°	0
85°	0



TEST NUMBER: P856663

CATALOG NUMBER: LD6C70D010 EU6709027 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	419.5	6.0
10°-20°	1260.9	18.1
20°-30°	1900.8	27.3
30°-40°	1945.6	27.9
40°-50°	1133.4	16.3
50°-60°	260.5	3.7
60°-70°	32.0	0.5
70°-80°	8.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3581.3	51.4
0°-40°	5526.8	79.4
0°-60°	6920.7	99.4
0°-90°	6961.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6961.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4349	
5°	4372	420
15°	4467	1261
25°	4167	1901
35°	3157	1946
45°	1460	1133
55°	253	260
65°	24	32
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P856663

CATALOG NUMBER: LD6C70D010 EU6709027 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4348.7
2.5°	4340.8
5°	4372.3
7.5°	4403.8
10°	4443.2
12.5°	4451.2
15°	4467.1
17.5°	4451.2
20°	4411.7
22.5°	4285.4
25°	4167.1
27.5°	3977.8
30°	3733.1
32.5°	3480.6
35°	3157.0
37.5°	2793.8
40°	2391.3
42.5°	1941.5
45°	1460.2
47.5°	1018.0
50°	670.9
52.5°	426.3
55°	252.6
57.5°	134.2
60°	71.0
62.5°	39.4
65°	23.6
67.5°	23.6
70°	15.9
72.5°	7.9
75°	7.9
77.5°	7.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)