

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685168

Luminaire Tested: **LX6C70D010 EX6709030 6LBNLI**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P685168
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6709030 6LBNLI
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5694.1 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685168
CATALOG NUMBER: LX6C70D010 EX6709030 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685168

CATALOG NUMBER: LX6C70D010 EX6709030 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	710683
5°	664609
10°	542041
15°	398873
20°	274926
25°	204103
30°	153315
35°	95606
40°	46408
45°	15916
50°	2089
55°	1577
60°	910
65°	1077
70°	1330
75°	0
80°	0
85°	0



TEST NUMBER: P685168

CATALOG NUMBER: LX6C70D010 EX6709030 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1077.9	18.9
10°-20°	1934.7	34.0
20°-30°	1564.2	27.5
30°-40°	901.1	15.8
40°-50°	190.5	3.3
50°-60°	16.4	0.3
60°-70°	8.2	0.1
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4576.7	80.4
0°-40°	5477.8	96.2
0°-60°	5684.7	99.8
0°-90°	5694.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5694.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12964	
5°	12077	###
15°	7028	1935
25°	3374	1564
35°	1429	901
45°	205	190
55°	16	16
65°	8	8
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685168

CATALOG NUMBER: LX6C70D010 EX6709030 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	12963.9
2.5°	12808.1
5°	12077.3
7.5°	11026.4
10°	9737.4
12.5°	8415.6
15°	7028.1
17.5°	5689.8
20°	4712.6
22.5°	3965.6
25°	3374.3
27.5°	2873.7
30°	2422.0
32.5°	1921.3
35°	1428.6
37.5°	993.4
40°	648.5
42.5°	394.2
45°	205.3
47.5°	82.0
50°	24.5
52.5°	24.5
55°	16.5
57.5°	16.5
60°	8.3
62.5°	8.3
65°	8.3
67.5°	8.3
70°	8.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)